



Lightech™
Halogen Transformer

901060010

LET 60W 12V

60W Class 2 electronic transformer. Potted. 120V input.

Current: AC

Availability: A



Specs

Power: 60.0 W

Input specs

Power factor: 0.95

Input current: 0.5-0.5 A

Input frequency: 60 Hz

Input voltage: 120.0-120.0 V

Output specs

Output voltage: 11.7 V

Output current range: 5000.0-5000.0 mA

Dimmable

Dimmable: true

Environment

Ta max: 50.0 °C

Tc: 90.0 °C

Standards

UL: E193999

Class 2: true

Mechanical

Potted: true

Input wire size AWG: 18.0 AWG

Case color: silver

Output wire size: 14.0 AWG

Weight: 0.085 kg

Output wire color: blue

Case material: Aluminum

Input wires color: black/white

Sales

Availability: A

Notes:

- Specifications may vary without notice
- Always consult National, State and local electrical codes
- IP67 products should never be immersed or exposed to direct rainfall
- Parameters are measured at rated output, rated load and at an ambient temperature of 25°C
- Expect slight variation including component tolerance, setup tolerance, line regulation and load regulation
- Power supplies should always be stress tested and tested for EMC within specific fixtures
- Where grounding/earthing is not indicated, avoid grounding/earthing or contact with grounded/earthed metal enclosures
- Performance with dimmers, where supported, may vary depending on dimmer model
- Subject to limited warranty (3yr for transformers, 5yr for drivers) terms and conditions as published from time to time

Manufacturer is responsible for FCC compliance of their final product.