



ScrubShield
Complies with UL514A

Floor Boxes

Flush Rectangular Stamped Steel Concrete Floor Boxes

Dimensions Inches (mm)

Stamped Steel

Style	1-Gang Deep	2-Gang Deep	3-Gang Deep	1-Gang Shallow	2-Gang Shallow	3-Gang Shallow	1-Gang Deep	1-Gang Shallow
Collar Material								
Brass	B2431*	B2432	B2433	B2421*	B2422	B2423	B2427*	B2429*
Aluminum	BA2431*	BA2432	BA2433	BA2421*	BA2422	BA2423	-	-
Min. Depth of Pour	3.75" (95.3)	3.75" (95.3)	3.75" (95.3)	2.75" (69.9)	2.75" (69.9)	2.75" (69.9)	4.00" (101.6)	3.00" (76.2)
Adjustability	Fully	Fully	Fully	Fully	Fully	Fully	Fully	Fully
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)
After Pour Internal Height Adjustment	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.38" (9.5)	.38" (9.5)
Cubic Inch (cm³) Capacity Per Gang	60.0 cu. in. (983.2 cm ³)	52.8 cu. in. (865.2 cm ³)	50.8 cu. in. (832.5 cm ³)	39.5 cu. in. (647.3 cm ³)	35.0 cu. in. (573.5 cm ³)	34.0 cu. in. (557.2 cm ³)	54.0 cu. in. (884.9 cm ³)	37.3 cu. in. (611.2 cm ³)
Dimensions – A	3.72" (94.5)	3.72" (94.5)	3.72" (94.5)	2.74" (69.6)	2.74" (69.6)	2.74" (69.6)	3.90" (99.1)	2.81" (71.4)
Dimensions – B	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)
Dimensions – C	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)	6.00" (152.4)	6.00" (152.4)
Dimensions – D	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.2)	4.38" (111.2)
Dimensions – E	3.19" (81.0)	6.44" (163.6)	9.67" (245.6)	3.19" (81.0)	6.44" (163.6)	9.67" (245.6)	3.19" (81.0)	3.19" (81.0)
Knockouts – Sides	(1) 3/4", (1) 1 1/4"	(2) 3/4", (1) 1 1/4"	(3) 3/4", (1) 1 1/4"	(2) 1/2", (1) 3/4"	(4) 1/2", (1) 3/4"	(6) 1/2", (1) 3/4"	(1) 1/2", (1) 1 1/4"	(2) 1/2", (1) 3/4"
Knockouts – Ends	(1) 3/4", (1) 1 1/4"	(1) 3/4", (1) 1 1/4"	(1) 3/4", (1) 1 1/4"	(1) 1/2", (1) 3/4"	(2) 1/2", (1) 3/4"	(2) 1/2", (1) 3/4"	(1) 3/4", (1) 1"	(1) 1/2", (1) 3/4"
Knockouts – Bottom	(2) 3/4", (1) 1 1/4"	(4) 3/4", (1) 1 1/4"	(6) 3/4", (1) 1 1/4"	(2) 3/4", (1) 1 1/4"	(4) 3/4", (1) 1 1/4"	(6) 3/4", (1) 1 1/4"	(3) 1/2", (2) 3/4"	(3) 1/2", (2) 3/4"
Concrete Cover Included	✓	✓	✓	✓	✓	✓	✓	✓
Closure Plugs Included	-	-	-	-	-	-	-	-
Removable LV Barrier	-	✓	✓	-	✓	✓	-	-

Note: UL File Number E92074.

CSA File Number LR18416.

* Suitable for single service applications only.

Flush Rectangular Floor Box Covers

	S3825	S3625	S3826	S2425	S2625	S2825	S3425	S3813
Brass	S3825	S3625	S3826	S2425	S2625	S2825	S3425	S3813
Aluminum	SA3825	SA3625	SA3826	SA2425	SA2625	-	-	SA3813
Dimensions	4.15" x 2.99"							
	Duplex Flap	Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4"	2 1/8" x 1"	2 1/8" Single Receptacle	2 3/8" Single Receptacle	Blank

Carpet Flanges

Tapered Flange	1-Gang	2-Gang	3-Gang
Number of Gangs	1-Gang	2-Gang	3-Gang
Dimensions	6.00" x 4.85"	6.00" x 8.13"	6.00" x 11.34"
Brass	SB3083	SB3084	SB3085
Aluminum	SA3083	SA3084	SA3085
Clear Polycarbonate	S3083	S3084	S3085