

# Floor Boxes

## Flush Rectangular Stamped Steel Concrete Floor Boxes

**ScrubShield**  
Complies with UL514A



### Dimensions Inches (mm)

### Stamped Steel

Style	1-Gang Deep			2-Gang Deep			3-Gang Deep			1-Gang Shallow			2-Gang Shallow			3-Gang Shallow			1-Gang Deep			1-Gang Shallow				
<b>Collar Material</b>	Brass			Aluminum			Brass			Aluminum			Brass			Aluminum			Brass			Aluminum				
<b>Min. Depth of Pour</b>	3.75" (95.3)			3.75" (95.3)			3.75" (95.3)			2.75" (69.9)			2.75" (69.9)			2.75" (69.9)			4.00" (101.6)			3.00" (76.2)				
<b>Adjustability</b>	Fully			Fully			Fully			Fully			Fully			Fully			Fully			Fully				
<b>Before Pour External Height Adjustment</b>	1.25" (31.8)			1.25" (31.8)			1.25" (31.8)			1.25" (31.8)			1.25" (31.8)			1.25" (31.8)			1.25" (31.8)			1.25" (31.8)				
<b>After Pour Internal Height Adjustment</b>	.50" (12.7)			.50" (12.7)			.50" (12.7)			.50" (12.7)			.50" (12.7)			.50" (12.7)			.38" (9.5)			.38" (9.5)				
<b>Cubic Inch (cm<sup>3</sup>) Capacity Per Gang</b>	60.0 cu. in. (983.2 cm <sup>3</sup> )			52.8 cu. in. (865.2 cm <sup>3</sup> )			50.8 cu. in. (832.5 cm <sup>3</sup> )			39.5 cu. in. (647.3 cm <sup>3</sup> )			35.0 cu. in. (573.5 cm <sup>3</sup> )			34.0 cu. in. (557.2 cm <sup>3</sup> )			54.0 cu. in. (884.9 cm <sup>3</sup> )			37.3 cu. in. (611.2 cm <sup>3</sup> )				
<b>Dimensions – A</b>	3.72" (94.5)			3.72" (94.5)			3.72" (94.5)			2.74" (69.6)			2.74" (69.6)			2.74" (69.6)			3.90" (99.1)			2.81" (71.4)				
<b>Dimensions – B</b>	4.81" (122.2)			4.81" (122.2)			4.81" (122.2)			4.81" (122.2)			4.81" (122.2)			4.81" (122.2)			4.81" (122.2)			4.81" (122.2)				
<b>Dimensions – C</b>	6.00" (152.4)			9.25" (235.0)			12.50" (317.5)			6.00" (152.4)			9.25" (235.0)			12.50" (317.5)			6.00" (152.4)			6.00" (152.4)				
<b>Dimensions – D</b>	4.38" (111.3)			4.38" (111.3)			4.38" (111.3)			4.38" (111.3)			4.38" (111.3)			4.38" (111.3)			4.38" (111.2)			4.38" (111.2)				
<b>Dimensions – E</b>	3.19" (81.0)			6.44" (163.6)			9.67" (245.6)			3.19" (81.0)			6.44" (163.6)			9.67" (245.6)			3.19" (81.0)			3.19" (81.0)				
<b>Knockouts – Sides</b>	(1) 3/4", (1) 1 1/4"			(2) 3/4", (1) 1 1/4"			(3) 3/4", (1) 1 1/4"			(2) 1/2", (1) 3/4"			(4) 1/2", (1) 3/4"			(6) 1/2", (1) 3/4"			(1) 1/2", (1) 1 1/4"			(2) 1/2", (1) 3/4"				
<b>Knockouts – Ends</b>	(1) 3/4", (1) 1 1/4"			(1) 3/4", (1) 1 1/4"			(1) 3/4", (1) 1 1/4"			(1) 1/2", (1) 3/4"			(2) 1/2", (1) 3/4"			(2) 1/2", (1) 3/4"			(1) 3/4", (1) 1"			(1) 1/2", (1) 3/4"				
<b>Knockouts – Bottom</b>	(2) 3/4", (1) 1 1/4"			(4) 3/4", (1) 1 1/4"			(6) 3/4", (1) 1 1/4"			(2) 3/4", (1) 1 1/4"			(4) 3/4", (1) 1 1/4"			(6) 3/4", (1) 1 1/4"			(3) 1/2", (2) 3/4"			(3) 1/2", (2) 3/4"				
<b>Concrete Cover Included</b>	✓			✓			✓			✓			✓			✓			✓			✓				
<b>Closure Plugs Included</b>	-			-			-			-			-			-			-			-				
<b>Removable LV Barrier</b>	-			✓			✓			-			✓			✓			-			-				

Note: UL File Number E92074.  
CSA File Number LR18416.  
\* Suitable for single service applications only.

### Flush Rectangular Floor Box Covers

	<b>S3825</b>	<b>S3625</b>	<b>S3826</b>	<b>S2425</b>	<b>S2625</b>	<b>S2825</b>	<b>S3425</b>	<b>S3813</b>
Brass	<b>S3825</b>	<b>S3625</b>	<b>S3826</b>	<b>S2425</b>	<b>S2625</b>	<b>S2825</b>	<b>S3425</b>	<b>S3813</b>
Aluminum	<b>SA3825</b>	<b>SA3625</b>	<b>SA3826</b>	<b>SA2425</b>	<b>SA2625</b>	-	-	<b>SA3813</b>
Dimensions 4.15" x 2.99"								
	Duplex Flap	Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	2 3/8" Single Receptacle	Blank

### Carpet Flanges

<b>Tapered Flange</b>	1-Gang	2-Gang	3-Gang
Number of Gangs	1-Gang	2-Gang	3-Gang
Dimensions	6.00" x 4.85"	6.00" x 8.13"	6.00" x 11.34"
Brass	<b>SB3083</b>	<b>SB3084</b>	<b>SB3085</b>
Aluminum	<b>SA3083</b>	<b>SA3084</b>	<b>SA3085</b>
Clear Polycarbonate	<b>S3083</b>	<b>S3084</b>	<b>S3085</b>