



## Switches

**15 and 20 Ampere, 120-277 Volts AC**


Specification Grade Commercial Series

**CSB120****Specification Grade Commercial Series,  
15A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Almond	<b>CSB115AL</b>	<b>CSB215AL</b>	<b>CSB315AL</b>	<b>CSB415AL</b>
	Black	<b>CSB115BK</b>	<b>CSB215BK</b>	<b>CSB315BK</b>	<b>CSB415BK</b>
	Brown	<b>CSB115</b>	<b>CSB215</b>	<b>CSB315</b>	<b>CSB415</b>
	Gray	<b>CSB115GY</b>	<b>CSB215GY</b>	<b>CSB315GY</b>	<b>CSB415GY</b>
	Ivory	<b>CSB115I</b>	<b>CSB215I</b>	<b>CSB315I</b>	<b>CSB415I</b>
	Light Almond	<b>CSB115LA</b>	<b>CSB215LA</b>	<b>CSB315LA</b>	<b>CSB415LA</b>
	White	<b>CSB115W</b>	<b>CSB215W</b>	<b>CSB315W</b>	<b>CSB415W</b>

**Specification Grade Commercial Series,  
20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Almond	<b>CSB120AL</b>	<b>CSB220AL</b>	<b>CSB320AL</b>	<b>CSB420AL</b>
	Black	<b>CSB120BK</b>	<b>CSB220BK</b>	<b>CSB320BK</b>	<b>CSB420BK</b>
	Brown	<b>CSB120</b>	<b>CSB220</b>	<b>CSB320</b>	<b>CSB420</b>
	Gray	<b>CSB120GY</b>	<b>CSB220GY</b>	<b>CSB320GY</b>	<b>CSB420GY</b>
	Ivory	<b>CSB120I</b>	<b>CSB220I</b>	<b>CSB320I</b>	<b>CSB420I</b>
	Light Almond	<b>CSB120LA</b>	<b>CSB220LA</b>	<b>CSB320LA</b>	<b>CSB420LA</b>
	Red	<b>CSB120R</b>	<b>CSB220R</b>	<b>CSB320R</b>	<b>CSB420R</b>
	White	<b>CSB120W</b>	<b>CSB220W</b>	<b>CSB320W</b>	<b>CSB420W</b>

**CS115I****Specification Grade Commercial Series,  
15A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, side wired only.	Almond	<b>CS115AL</b>	—	<b>CS315AL</b>	—
	Black	<b>CS115BK</b>	—	<b>CS315BK</b>	—
	Brown	<b>CS115</b>	—	<b>CS315</b>	—
	Gray	<b>CS115GY</b>	—	<b>CS315GY</b>	—
	Ivory	<b>CS115I</b>	—	<b>CS315I</b>	—
	Light Almond	<b>CS115LA</b>	—	<b>CS315LA</b>	—
	White	<b>CS115W</b>	—	<b>CS315W</b>	—

**Specification Grade Commercial Series,  
20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, side wired only.	Almond	<b>CS120AL</b>	—	<b>CS320AL</b>	—
	Black	<b>CS120BK</b>	—	<b>CS320BK</b>	—
	Brown	<b>CS120</b>	—	<b>CS320</b>	—
	Gray	<b>CS120GY</b>	—	<b>CS320GY</b>	—
	Ivory	<b>CS120I</b>	—	<b>CS320I</b>	—
	Light Almond	<b>CS120LA</b>	—	<b>CS320LA</b>	—
	White	<b>CS120W</b>	—	<b>CS320W</b>	—

Note: See page C-11 for pre-wired/leaded devices.  
See page C-15 for accessories.  
See page C-16 for wallplates.  
See page C-18 for wiring diagrams.  
For pre-wired/leaded devices see page C-11.

**HP Conversion Chart**

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP