



Circuit Guard®

Portable GFCI Single Outlet - 12/3 SJEOW

15A 120V AC

Description	Catalog Number
2' (60.9 cm) GFCI line cord, automatic set.	GFP2CA
2' (60.9 cm) GFCI line cord, manual set.	GFP2CM
25' (762.0 cm) GFCI line cord, automatic set.	GFP25CA
25' (762.0 cm) GFCI line cord, manual set.	GFP25CM



GFP2CA

Circuit Guard®

Portable GFCI Triple Tap Outlet - 12/3 SJEOW

15A 120V AC

Description	Catalog Number
2' (60.9 cm) GFCI line cord, automatic set.	GFP2TTA
2' (60.9 cm) GFCI line cord, manual set.	GFP2TTM
25' (762.0 cm) GFCI line cord, automatic set.	GFP25TTA
25' (762.0 cm) GFCI line cord, manual set.	GFP25TTM



GFP2TTA

Circuit Guard®

OEM Equipment Integrated Cord Sets - 14/3 SJEOW

15A 120V AC

Description	Catalog Number
15' (457.2 cm) GFCI with flying leads, automatic set.	GFP15LA
15' (457.2 cm) GFCI with flying leads, manual set.	GFP15LM
35' (1066.8 cm) GFCI with flying leads, automatic set.	GFP35LA
35' (1066.8 cm) GFCI with flying leads, manual set.	GFP35LM



GFP15LA

15A GFCI In Line GFCI, Single and Triple Tap - 12/3 SJTW

15A 120V AC

Description	Catalog Number
2' (60.9 cm), 5-15 single tap, automatic set.	GFPIL15125A
2' (60.9 cm), 5-15 single tap, manual set.	GFPIL15125M
2' (60.9 cm), 5-15 triple tap, automatic set.	GFPIL15125TRIA
2' (60.9 cm), 5-15 triple tap, manual set.	GFPIL15125TRIM



GFPIL15125TRIM

20A GFCI In Line GFCI, Locking - 12/3 SJTW

20A 120V AC

Description	Catalog Number
2' (60.9 cm), L5-20 locking, automatic set.	GFPIL20125LKA
2' (60.9 cm), L5-20 locking, manual set.	GFPIL20125LKM

20A GFCI In Line GFCI, Locking - 12/3 SJTW

20A 250V AC

Description	Catalog Number
2' (60.9 cm), L6-20 locking, automatic set.	GFPIL20250LKA
2' (60.9 cm), L6-20 locking, manual set.	GFPIL20250LKM



GFPIL20125LKA

Specifications

Portable GFCI Line Cords

Trip Level	4 to 6 mA.
Trip Time	.025 sec. nominal.
Frequency	60 Hz.
Voltage	120/250V AC +10% - 15%. Incorporates no voltage release feature.
Current	15A/20A.
Maximum Interrupting Capacity	2000A.
Operating Temperature	-35°C to 66°C or -30°F to 150°F.
Maximum Humidity	95%.
Housing	High-impact, UV stabilized PVC. UL 94V-0 flammability classification. Meets UL and CSA watertight requirements. Adhesive bonded.
Visual Fault Indication Light On	Indicates fault.
Listing and Standards	Meets UL943 Class A, UL File E41978. CSA Certified.
Code	Meets all NEC® and CEC requirements.



GFPIL20250LKM

NEC® is a registered trademark of the National Fire Protection Association (NFPA).