

Marine Products

30 Ampere, 125 Volt Twist-Lock® Devices

2 Pole, 3 Wire

Ship-to-Shore Devices



HBL26CM10



HBL26CM11



HBL60CM31



HBL26CM13



HBL60CM33



HBL60CM32

30A 125V Ship-to-Shore Devices

| Description | Catalog Number |
|--|-----------------------|
| Yellow single receptacle has Rynite® body and abuse resistant nylon face. IP20 SUITABILITY. | HBL26CM10 |
| Yellow Insulgrip® plug has rugged nylon housing and cord grip with range of .36-.93 in. (9-24) that utilizes a unique offset jaws arrangement to provide secure strain relief. IP20 SUITABILITY. | HBL26CM11 |
| Yellow Seal-Tite® cover for weatherproofing HBL26CM11 plugs. IP55 SUITABILITY. Note: Fits Insulgrip devices only. | HBL60CM31+ |
| White Seal-Tite cover for weatherproofing HBL26CM11 plugs. IP55 SUITABILITY. Note: Fits Insulgrip devices only. | HBL60CM31W+ |
| Yellow Insulgrip connector body has rugged nylon housing and cord grip with range of .36-.93 in. (9-24) that utilizes a unique offset jaws arrangement to provide secure strain relief. | HBL26CM13 |
| Yellow Seal-Tite cover for weatherproofing HBL26CM13 connector bodies when used with shore power inlets. Threaded sealing ring makes connection watertight. Also for weatherproofing HBL26CM11 plug when used with HBL303SSO power outlet. IP56 SUITABILITY. Note: Fits Insulgrip devices only. | HBL60CM33+ |
| White Seal-Tite cover for weatherproofing HBL26CM13 connector body when used with shore power inlets. Threaded sealing ring makes connection watertight. Also for weatherproofing HBL26CM11 plug when used with HBL303SSO power outlet. IP56 SUITABILITY. Note: Fits Insulgrip devices only. | HBL60CM33W+ |
| Yellow Seal-Tite cover for weatherproofing HBL26CM13 connector bodies when used on extension cords or adapters. IP55 SUITABILITY. Note: Fits Insulgrip devices only. | HBL60CM32+ |
| Yellow polycarbonate spring-loaded lift cover for weatherproofing old style 26CM10 receptacle. Meets the most stringent requirements of UL's three listing categories for weatherproof plates. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY. | HBL74CM24WO** |
| Same as HBL74CM24WO except gray in color. IP44 SUITABILITY. | HBL7424WO** |
| Yellow polycarbonate spring-loaded lift cover for weatherproofing HBL26CM10 receptacle. Meets the most stringent requirements of UL's three listing categories for weatherproof plates. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY. | HBL74CM25WOA** |
| Same as HBL74CM25WOA except white in color. IP44 SUITABILITY. | HBL74CM25WOAW |
| Same as HBL74CM25WOA except gray in color. IP44 SUITABILITY. | HBL7425WOA** |
| Stainless steel wall plate for old 26CM10. | SS725 |
| Stainless steel wall plate for new HBL26CM10. | SS720 |

Note: ** See page W-45 for accessories.
+ Boots are not UL listed.

Rynite® is a registered trademark of E. I. DuPont.