



Dimensions Inches (mm)	Stamped Steel			Cast Iron
Style	4-Gang Deep	4-Gang Shallow	8-Gang Deep	4-Gang Shallow
	<p>HBLCFB301BASE</p>	<p>HBLCFB401BASE</p>	<p>HBLCFB501BASE</p>	<p>HBLCFB401CB</p>
Min. Depth of Pour	4.25" (108)	3.00" (76)	5.25" (133)	3.25" (83)
Adjustability	Before pour	Before pour	Before pour	Before pour
Cubic Inch (cm ³) Capacity Per Chamber	29.5 cu. in. (483 cm ³)	25.5 cu. in. (418 cm ³)	49.5 cu. in. (811 cm ³)	25.5 cu. in. (418 cm ³)
Dimensions – A	4.0" (102)	2.63" (67)	5.13" (130)	3.13" (80)
Dimensions – B	10.0" (254)	10.0" (254)	10.0" (254)	10.0" (254)
Dimensions – C	10.0" (254)	10.0" (254)	10.0" (254)	10.0" (254)
Threaded Access Holes – Per Chamber	–	–	–	(2) 1"
Knockouts – Per Chamber	(1) Concentric 1/2", 3/4" (1) Concentric 3/4", 1" (1) 1 1/4"	(3) Concentric 1/2", 3/4"	(1) Concentric 1/2", 3/4" (1) Concentric 3/4", 1" (1) 1 1/4"	–
Concrete Cover Included	✓	✓	✓	✓
Closure Plugs Included	–	–	–	✓

Note: UL File Number E197203. CSA File Number LR702145.

Floor Box Covers with Carpet Recess

Die cast metal cover and flange assembly

Granite	HBLTCGNTSW
Black	HBLTCGNTBKS



Accessories

On-Grade Barrier
The on-grade barrier is intended for use on installations at grade level. This accessory is installed prior to the concrete pour and provides a barrier between the soil. The on-grade barrier comes with leveling feet and anchor points.

CFBOGPAN4

Pour Pan Dimensions:
15.75 in. sq.
4 in. depth

Hubbell Screw Type Face Plates**

<p>HBLST302Sxx</p> <p>Duplex</p>	<p>HBLDE301Sxx</p> <p>Style Line® Decorator</p>	<p>HBLTO310Sxx</p> <p>Toggle</p>	<p>HBLTL318Sxx</p> <p>Single Receptacle (1.56" Boss Dia.)</p>
<p>HBLTL319Sxx</p> <p>Single Receptacle (1.39" Boss Dia.)</p>	<p>HBLBL300Sxx</p> <p>Blank</p>	<p>HBLIMFSxx</p> <p>3-Unit Hubbell iSTATION (See Section C for module options)</p>	<p>HBL317Sxx</p> <p>Hubbell 6-Port</p>

xx = Color: **BK** (Black), **GY** (Gray), **I** (Ivory) and **WA** (White).

ScrubShield
Complies with UL514 A & C

