

# IEC Pin and Sleeve Unfused Circuit-Lock® Devices

20, 30, 60 and 100 Ampere – North American Ratings, 32 Ampere – International Rating

IP67  
SUITABILITY



Rating					Unfused Circuit-Lock® Devices	
Amps	Poles and Wires	Configuration Recep.	Plug	AC Voltage	Mechanical Interlock	Mating Plug
20	3P 4W			120/240V	HBL420MI12W	HBL420P12W
	3P 4W			3Ø 240V	HBL420MI9W	HBL420P9W
	3P 4W			3Ø 480V	HBL420MI7W	HBL420P7W
	3P 4W			3Ø 600V	HBL420MI5W	HBL420P5W
30	2P 3W			120V	HBL330MI4W	HBL330P4W
	2P 3W			240V	HBL330MI6W	HBL330P6W
	2P 3W			480V	HBL330MI7W	HBL330P7W
	3P 4W			120/240V	HBL430MI12W	HBL430P12W
	3P 4W			3Ø 240V	HBL430MI9W	HBL430P9W
	3P 4W			3Ø 480V	HBL430MI7W	HBL430P7W
	3P 4W			3Ø 600V	HBL430MI5W	HBL430P5W
	4P 5W			3ØY 120/208V	HBL530MI9W	HBL530P9W
	4P 5W			3ØY 277/480V	HBL530MI7W	HBL530P7W
	4P 5W			3ØY 347/600V	HBL530MI5W	HBL530P5W
32	3P 4W			380V 50HZ-440V 60Hz	HBL432MI3W	HBL432P3W
60	2P 3W			120V	HBL360MI4W	HBL360P4W
	2P 3W			240V	HBL360MI6W	HBL360P6W
	2P 3W			480V	HBL360MI7W	HBL360P7W
	3P 4W			120/240V	HBL460MI12W	HBL460P12W
	3P 4W			3Ø 240V	HBL460MI9W	HBL460P9W
	3P 4W			3Ø 480V	HBL460MI7W	HBL460P7W
	3P 4W			3Ø 600V	HBL460MI5W	HBL460P5W
	4P 5W			3ØY 120/208V	HBL560MI9W	HBL560P9W
	4P 5W			3ØY 277/480V	HBL560MI7W	HBL560P7W
	4P 5W			3ØY 347/600V	HBL560MI5W	HBL560P5W
100	2P 3W			240V	HBL3100MI6W	HBL3100P6W
	3P 4W			120/240V	HBL4100MI12W	HBL4100P12W
	3P 4W			3Ø 240V	HBL4100MI9W	HBL4100P9W
	3P 4W			3Ø 480V	HBL4100MI7W	HBL4100P7W
	3P 4W			3Ø 600V	HBL4100MI5W	HBL4100P5W
	4P 5W			3ØY 120/208V	HBL5100MI9W	HBL5100P9W

Note: 20, 30 and 32A – 1 inch N.P.T. hub supplied; 60 and 100A – 1¼ inch hub supplied.

