

Switched Enclosures

Circuit-Lock® Unfused Disconnect Switches

"Suitable as Motor Disconnect"



UL Listed, CSA Certified
TYPE 4, 4X and
12 Enclosure Rating

30, 60 and 100 Amp Unfused Disconnect Switches

Description	Catalog Number
30A Circuit-Lock disconnect switch.	HBLDS3
30A Circuit-Lock disconnect switch for use with variable frequency drives.	HBLDS3VFD ^A
30A Circuit-Lock disconnect switch with HBLAC1 aux. contact.	HBLDS3AC
30A Circuit-Lock disconnect switch with HBLAC2 aux. contact.	HBLDS3AC2
30A Circuit-Lock disconnect switch without conduit knockout or conduit fitting.	HBLDS3NK
30A Circuit-Lock disconnect switch with HBLAC1 aux. contact without conduit knockout or conduit fitting.	HBLDS3ACNK
30A Circuit-Lock disconnect switch with 3 aux. contacts, w/o conduit knockouts. Break before main break – 1 set "normally open", 1 set "normally closed". Break after main break – 2 sets "normally open", 1 set "normally closed".	HBLDS33ACNK
60A Circuit-Lock disconnect switch.	HBLDS6
60A Circuit-Lock disconnect switch with HBLAC1 aux. contact.	HBLDS6AC
100A Circuit-Lock disconnect switch.	HBLDS10
100A Circuit-Lock disconnect switch with HBLAC1 aux. contact.	HBLDS10AC



HBLDS3AC



HBLAC1



HBLAC2

Auxiliary Contacts for 30, 60 and 100 Amp Switch, A600 Pilot Duty

Description	Catalog Number
"Break After Main Break", 1 set of n/o contacts, 1 set of n/c contacts.	HBLAC1*
"Break Before Main Break", 1 set of n/o contacts.	HBLAC2*

Ground Block

Description	Catalog Number
For 30A switches.	HBL30RGB
For 60A and 100A switches.	HBL60100RGB

Neutral Block

Description	Catalog Number
For 30A switches.	HBL30RNB
For 60A switches.	HBL60RNB
For 100A switches.	HBL100RNB



HBL30RGB



HBL30RNB

Note: * Not for use with HBLDS33ACNK.
30A Units are supplied with one 3/4 in. N.P.T. Raintight conduit fitting.
60A and 100A Units are supplied with two 1 1/4 in. N.P.T. Raintight conduit fittings.
^A See page C-34 for wiring details.