



Stamped Covers

Stamped Covers with Integral Neoprene Gasket

Stamped Covers

Cast Covers with Integral Neoprene Gasket

**FEATURES-SPECIFICATIONS**



**Stamped Material/Finish**

**Aluminum**

- Gasketed 316 Stainless steel screws
- Natural finish

**Galvanized Steel**

- 316 Stainless steel screws
- Natural finish

**Gasket**

- Neoprene

**Cast Material/Finish**

**Copper-free Aluminum**

(less than 4/10 of 1%)

- Electrostatically applied powder coating

**Duraloy Gray Iron Alloy**

- Tri-coat finish of electrozinc, chromate sealant, and electrostatically applied powder coating
- Gasketed 316 Stainless steel screws

STAMPED ALUMINUM AND STAMPED STEEL COVERS WITHOUT AND WITH GASKETS								
CATALOG NUMBER				HUB SIZE	DIMENSIONS			
ALUMINUM W/O GASKET	ALUMINUM W/GASKET	STEEL W/O GASKET	STEEL W/GASKET		LENGTH	WIDTH	HEIGHT*	
170SA	170GSA	170	170G	1/2"	3-11/16" (94)	1-3/8" (35)	5/16" (8)	
270SA	270GSA	270	270G	3/4"	4-1/4" (108)	1-1/2" (32)	5/16" (8)	
370SA	370GSA	370	370G	1"	5" (127)	1-3/4" (44)	5/16" (8)	
470SA	470GSA	470	470G	1-1/4"	5-1/2" (140)	2-3/16" (56)	5/16" (8)	
570SA	570GSA	570	570G	1-1/2"	6" (152)	2-7/16" (62)	5/16" (8)	
670SA	670GSA	670	670G	2"	7" (178)	3" (76)	5/16" (8)	
870SA	870GSA	870	870G	2-1/2"	9" (229)	4-1/4" (108)	9/16" (14)	
870SA	870GSA	870	870G	3"	9" (229)	4-1/4" (108)	9/16" (14)	
970SA	970GSA	970	970G	3-1/2"	11" (279)	5-1/4" (133)	9/16" (14)	
970SA	970GSA	970	970G	4"	11" (279)	5-1/4" (133)	9/16" (14)	

\*For covers with integral gasket, add 1/8" (3) to height.

CAST ALUMINUM AND CAST IRON COVERS WITHOUT AND WITH GASKETS								
CATALOG NUMBER				HUB SIZE	DIMENSIONS			
ALUMINUM W/O GASKET	ALUMINUM W/GASKET	STEEL W/O GASKET	STEEL W/GASKET		LENGTH	WIDTH	HEIGHT*	
170CSA	170CGSA	170C	170CG	1/2"	3-11/16" (94)	1-3/8" (35)	5/16" (8)	
270CSA	270CGSA	270C	270CG	3/4"	4-1/4" (108)	1-1/2" (32)	5/16" (8)	
370CSA	370CGSA	370C	370CG	1"	5" (127)	1-3/4" (44)	5/16" (8)	
470CSA	470CGSA	470C	470CG	1-1/4"	5-1/2" (140)	2-3/16" (56)	5/16" (8)	
570CSA	570CGSA	570C	570CG	1-1/2"	6" (152)	2-7/16" (62)	5/16" (8)	
670CSA	670CGSA	670C	670CG	2"	7" (178)	3" (76)	5/16" (8)	
870CSA	870CGSA	870C	870CG	2-1/2"	9" (229)	4-1/4" (108)	9/16" (14)	
870CSA	870CGSA	870C	870CG	3"	9" (229)	4-1/4" (108)	9/16" (14)	