



P4D - High Performance Parabolic

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
P4D00162	P4D22-232U6G-MA33-AV-EU	078531006501	2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Air w/Vanes			•			32.0	28	
P4D00120	P4D22-232U6G-MA33-S-EU	078531043445	2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Static	•	•	•	•	•	32.0	28	
P4D00156	P4D24-232G-MA26-S-EU	078531043704	2 x 4, 2-L, 12 Cell MA Lvr, 120-277V T8 Elec Ballast, Static	•	•	•	•	•	32.0	16	
P4D00157	P4D24-332G-MA36-AV-3EU	078531043711	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Air w/Vanes			•	•	•	33.0	16	
P4D00146	P4D24-332G-MA36-S-3EU	078531043483	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static	•	•	•	•	•	33.0	16	
93043905	P4D24-332G-MA36-S-3EPU	078531023331	2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Prog Start Ballast, Static		•				33.0	16	
P4D00138	P4D24-332G-MA36-S-EU	078531043414	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V T8 Elec (2 Ballasts), Static	•	•	•	•	•	35.0	16	
93043906	P4D24-332G-MA36-S-EPU	078531023348	2x4, 3-L, 18 Cell MA Lvr, 120-277V T8 Elec Prog Start (2) Ballasts, Static		•				33.0	16	
P4D00143	P4D24-332G-MA36-S-3EU- FO735	078531043476	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed		•	•	•	•	34.0	16	
P4D00119	P4D24-332G-MA36-S-3EU- FO735-C388	078531043261	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Stat, T8 Lamps Installed, 3 Wire Flex	•			•	•	34.0	16	
93043907	P4D24-332G-MA36-S-3EU- FO741	078531023355	2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed		•				34.0	16	
P4D00147	P4D24-432G-MA48-S-4EU	078531043490	2 x 4, 4-L, 32 Cell, 120-277V 4-L T8 Elec Ballast, Static		•	•	•	•	34.0	16	
P4D019047.16PK1	LVR P4D24 3X6 MA HK BAG	078531044985	Louver for 2 x 4, 18 cell, MA	•	•	•	•	•	10.0	N/A	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

MODEL	NO. OF LAMPS	CEILING TYPE	CELLS WIDE BY CELLS LONG	BALLAST	VOLTAGE
P4D High Performance Parabolic	2 Two 3 Three 4 Four (N/A in 2 x 2)	G Grid	33 3 x 3 (2' x 2' only) 26 2 x 6 (2' x 4' 2-Lamp only) 36 3 x 6 (2' x 4' 3-Lamp only) 48 4 x 8 (2' x 4' 4-Lamp only)	E 2-Lamp Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP T8, Programmed Start 3EP 3-Lamp T8, Programmed Start 4EP 4-Lamp T8, Programmed Start 24E 2 or 4-Lamp Electronic T8, Instant Start (For 3-Lamp Master/Satellite only) ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start	U 120V-277V
SIZE	LAMP TYPE	LOUVER FINISH	AIR HANDLING	OPTIONS	
22 2' x 2' 24 2' x 4'	17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-Lamp only)	MA Matte Anodized Low Iridescent Semi-Specular Aluminum (Std.)	S Static	FO735 35K 75CRI Full Wattage T8 Lamps Installed FO741 41K 75CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed C388 3-Wire Flex C488 4-Wire Flex EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 MS11 Master/Satellite w/ 11' Harness	

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.