



Actual

Catalog Number: 10CA
Product ID: 7TAH006150R0000
UPC Number: 78378620057
Status: Active

Type CA Aluminum Split-Bolt Connector with Spacer and Washer for Use on Copper, Aluminum Conductors. Conductor Range for Equal Main and Tap 2/0 Str.-2 Sol.

- Bolt, nut, pressure bar and contoured spacer of aluminum alloy. Pressure bar and contoured spacer made of electrolytic copper. Spacer is completely tin plated.
- Bolt and nut are anodized to prevent seizing of threads and reduce galvanic corrosion when in contact with copper conductor.
- Splicing, tapping or terminating conductors in power and grounding electrical connection.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Split-Bolt
Special Features	Bolt, nut, pressure bar and contoured spacer of aluminum alloy. Pressure bar and contoured spacer made of electrolytic copper. Spacer is completely tin plated.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Aluminum
Color	Metallic

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6.75x3.63x5.3
Outer Quantity	250
Outer Dimensions (inches)	21x11.75x8
Weight Uom	22 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com