



Actual

Catalog Number: 13-265
Product ID: 7TAA008010R0063
UPC Number: 78378600364
Status: Active

Wire Tie Nylon Ultra-Violet Resistant for Temperatures up to 105 Degrees Celsius (220 F)
 Length of 365mm (14.37 Inches) Tensile Strength Rating of 540 Newtons (120 Pounds)

North American Specifications (UNSPSC)

| | |
|------------------|---------------------------------|
| UNSPSC | 39121703 Cable ties |
| IGCC | 5034 Cable ties |
| Brand Name | T&B Electricians' Supplies |
| Type | Fasteners & Wiring Accessories |
| Length | 14.37 Inches/365mm |
| Bundle Diameter | Max 4 Inches/101.6mm |
| Material | Nylon/Polyamide 6.6 |
| Color | Black |
| Lock Mechanism | Double Locking Head |
| Tensile Strength | 120 Pounds/540 Newtons |

Packaging

| | |
|----------------|-------------------|
| Inner Quantity | 50 |
| Outer Quantity | 250 |
| Weight Uom | 1.63 lbs. per 100 |

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com