



Actual

Catalog Number: ADR60AR
Product ID: 7TAH006600R0243
UPC Number: 78378614980
EAN Number: 05415022245479
Status: Active

Type ADR-ALCUL Anti-Rotational Single-Conductor, One-Hole Mount, Conductor Range Max 600 MCM, Min 2 AWG, 1/2 Inch Bolt Hole, Tin Plated

- Unique bottom rib keeps the conductor from turning. Eliminates the need for excessive torque, which can damage large conductors.
- Bottom rib prevents conductor from loosening, even in heavy-vibration applications.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Anti-Rotational Mechanical Connector
Special Features	Unique bottom rib keeps the conductor from turning. Eliminates the need for excessive torque, which can damage large conductors.
Standard	UL E9809
Number Of Conductors	1
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	2-600
Number Of Mounting Holes	1
Mounting Hole Spacing	1/2 Inch

Packaging

Inner Quantity	6
Inner Dimensions (inches)	5.3x3.8x2.8
Outer Quantity	60
Outer Dimensions (inches)	15.3x8x5.6
Weight Uom	34.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com