



Actual

**Catalog Number:** ADR80-12D  
**Product ID:** 7TAH006600R0247  
**UPC Number:** 78378661039  
**Status:** Active

Type ADR-ALCUL Single-Conductor, Two-Hole Mount, Conductor Range (AL or CU) Max 800 kcmil, Min 300 kcmil, 1/2 Inch Bolt Hole, NEMA Spacing 1-3/4 Inch Centers, Length 6-3/19 Inch, Tin Plated

- Easy Installation - no special tools required.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Dual-Rated Mechanical Connector
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Number Of Conductors	1
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	300-800
Number Of Mounting Holes	2
Mounting Hole Spacing	1/2 Inch

### Packaging

Inner Quantity	3
Inner Dimensions (inches)	9.5x6x3.8
Outer Quantity	30
Outer Dimensions (inches)	17x11.25x8.75
Weight Uom	94 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000390

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)