



Remote Lighting Fixtures

Square



RERS

Injection molded housing. Surface mounted. Semi-recessed or recessed mounting available with kit. Black box, white trim. Single (RERS-1) and twin (RERS-2) lamp models. Dimensions and mounting kits same as Lite².

INCANDESCENT WEDGE BASE		
MODEL NUMBERS	LAMP VOLTS	LAMP WATTS
RERS-1-0609	6	9
RERS-2-0607	6	7

MODEL	DESCRIPTION
F-SRM	Semi-recessed mounting kit
-FRM	Fully-recessed option

Recessed Rectangle



124R

Recessed mounted fixture with frosted lens. White trim. Dimensions: 8³/₁₆" x 4¹/₂" x 4"

DC BAYONET BASE		
MODEL NUMBERS	LAMP VOLTS	LAMP WATTS
124R-0628	6	28
124R-1228	12	28

Recessed Eyeball



133

Adjustable to 42° and rotated through 358°. White standard, other finishes upon request. Dimensions: Trim ring: 4⁷/₈" dia. Back box: 4³/₁₆" deep x 4" dia.

DC BAYONET BASE		
MODEL NUMBERS	LAMP VOLTS	LAMP WATTS
133-0618	6	18
133-1228	12	28

Gimbal



122

Adjustable (60° max.) recessed mounted fixture. Matte white trim. Dimensions: 8¹/₂" dia. x 4¹/₂"

INCANDESCENT PAR 36 SEALED BEAM		
MODEL NUMBERS	LAMP VOLTS	LAMP WATTS
122SB-0625	6	25

LZ Series Matching Remote Lighting Heads

LZR

Architectural/commercial design. High performance MR-16 halogen lamps standard. Mounts to standard electrical boxes using universal mounting plate provided. Fixture housing mounts to back plate in a choice of four mounting positions. Housings secured using locking screws provided.



SINGLE REMOTE HEAD - WHITE	SINGLE REMOTE HEAD - BLACK	LAMP VOLTS	LAMP WATTS
LZRSW0605	LZRSB0605	6	5
LZRSW0610	LZRSB0610	6	10
LZRSW1205	LZRSB1205	12	5
LZRSW1210	LZRSB1210	12	10

TWIN REMOTE HEAD - WHITE	TWIN REMOTE HEAD - BLACK	LAMP VOLTS	LAMP WATTS
LZRDW0605	LZRDB0605	6	5
LZRDW0610	LZRDB0610	6	10
LZRDW1205	LZRDB1205	12	5
LZRDW1210	LZRDB1210	12	10

C1D2R/C1D2TR

Suitable for wet and damp location applications. Rated for NEC Class I, Division 2, Groups B, C and D as well as Class I, Zone 2, Group IIB + H₂ environments. Black housing and head assemblies. Single (C1D2R) and twin (C1D2TR) head models.



3R Listed

MODEL NUMBERS		LAMPS*	
SINGLE HEAD HUB LEFT SIDE ^{1,2}	TWIN HEAD HUB LEFT SIDE ^{1,2}	VOLTS	WATTS
C1D2R-6V8W	C1D2TR-6V8W	6	8
C1D2R-6V12W	C1D2TR-6V12W	6	12
C1D2R-12V8W	C1D2TR-12V8W	12	8
C1D2R-12V12W	C1D2TR-12V12W	12	12

* PAR 36 Halogen sealed beam lamps.

¹Hub Right Side — add "R" to end of model number. Example C1D2R-6V8WR.

²Hubs Both Sides — add "F" to end of model number. Example C1D2R-6V8WF.

Replacement lamp part numbers and photometrics are available on the web at www.dual-lite.com.

Dual-Lite Life Safety Products • www.dual-lite.com

A Hubbell Lighting, Inc. brand with representatives' offices in principal cities throughout North America.

Copyright © Hubbell Lighting, Inc., All Rights Reserved • Specifications subject to change without notice. • Printed in U.S.A.



HUBBELL LIGHTING, INC.

0602008 Rev C 6/09