



Remote Lighting Heads

SRH Series Standard Remote Lighting Heads

Catalog Number	
Comments	Type

FEATURES

Injection molded thermoplastic lamphead/round mounting plate assemblies. Mounts to 3 1/2" octagonal or single gang boxes. For use with most commercial or industrial emergency fixtures. Standard finish is available in white or black. Single and twin lamp fixtures with a choice of incandescent or halogen PAR 36 lamps.



ORDERING GUIDE

SRH	S	W	0620
Series	Heads	Finish	Lamp
	S Single D Double	W White B Black	0605 6 volt, 5.4 watts Incandescent ¹ 0607 6 volt, 7.2 watts Incandescent ¹ 0608 6 volt, 8 watts Halogen 0612 6 volt, 12 watts Halogen 0618 6 volt, 18 watts Incandescent 0620 6 volt, 20 watts Halogen 0625 6 volt, 25 watts Incandescent 1207 12 volt, 7.2 watts Incandescent ¹ 1208 12 volt, 8 watts Halogen 1212 12 volt, 12 watts Halogen 1218 12 volt, 18 watts Incandescent 1225 12 volt, 25 watts Incandescent 1235 12 volt, 35 watts Incandescent 2409 24 volt, 9 watts Incandescent ¹

¹Sealed Beam Type Lamp

OMS Series Outdoor Remote Lighting Heads

Catalog Number	
Comments	Type

FEATURES

Outdoor aluminum spot with sealed lamp and swivel assembly. Furnished with round gasketed aluminum mounting plate. Mounts to 3 1/2" octagonal boxes.



ORDERING GUIDE

OMS	S	W	0620
Series	Heads	Finish	Lamp
	S Single D Double	W White B Black	0605 6 volt, 5.4 watts Incandescent ¹ 0607 6 volt, 7.2 watts Incandescent ¹ 0608 6 volt, 8 watts Halogen 0612 6 volt, 12 watts Halogen 0618 6 volt, 18 watts Incandescent 0620 6 volt, 20 watts Halogen 0625 6 volt, 25 watts Incandescent 1207 12 volt, 7.2 watts Incandescent ¹ 1208 12 volt, 8 watts Halogen 1212 12 volt, 12 watts Halogen 1218 12 volt, 18 watts Incandescent 1225 12 volt, 25 watts Incandescent 1235 12 volt, 35 watts Incandescent 1250 12 volt, 50 watts Incandescent

¹Sealed Beam Type Lamp



Hubbell Lighting, Inc.

Replacement lamp part numbers and photometrics are available on the web at www.dual-lite.com.