

Lamps

Compact Fluorescent Lamps



MLS13GUWW
13w self-ballasted CFL lamp. GU24 base.

MLS18GUWW
18w self-ballasted CFL lamp. GU24 base.

MLS26GUWW
26w self-ballasted CFL lamp. GU24 base.

MLS32GUWW
32w self-ballasted CFL lamp. GU24 base.

MLS42GUWW
42w self-ballasted CFL lamp. GU24 base.



MLS13GUSWW6
13w self ballasted squat GU24 lamp. 2700K, 900 lumens.



MLS18GUSWW6
18w self ballasted squat GU24 lamp. 2700K, 1250 lumens.



MLS26GUSWW
26w self ballasted squat GU24 lamp. 2700K, 1650 lumens.

Halogen Lamps



P7829-01
35w MR11 GU4 MFL lamp, 12v.

P7830-01*
35w MR11 GU4 MFL coated lamp, 12v.



P7831-01
50w MR16 GU5.3 MFL lamp, 12v.

P7832-01*
50w MR16 GU5.3 MFL coated lamp, 12v.



P7833-01
50w GU10 MFL lamp, 120v.



P7834-01*
50w GU10 MFL coated lamp, 120v.

* Coated lamp eliminates pink color behind lamp.



P7802-01 20w G4 halogen, 12-volt.



P7805-01 50w mini candelabra halogen, 120 volt.

Xenon Lamps



P7800-01 5w 12-volt Xenon replacement lamp. 8,000 hour rated life.



P7807-01 60w krypton replacement lamp 60w Krypton, 120-volt. E12 (candelabra)



P7812-01 35w G9 halogen, 120-volt.



P7818-01 6-pack of 60w G9 halogen, 120-volt.



P7801-01 18w T5 wedge base lamp, 12-volt.

Socket Collar Tool



P8637-01 Socket collar tool
The socket collar tool was designed to provide extra leverage and eliminate a loose fit when installing glass shades. Working like a wrench, the socket collar tool extends into the shade and tightens the socket ring, securing the shade in place,

and can reverse to loosen the ring to remove the shade. This new accessory can be used on a variety of fixtures, including chandeliers, mini-pendants, sconces and wall brackets. For use on medium base lamp fixtures only.