

## 074011262 -- Deluxe Cord Grips



Straight Male

Deluxe Cord Grips completely eliminate pull tension on terminals, control cable arc-of-bend, prevent cord pull-out, and provide a liquidtight seal. They are offered with either aluminum, stainless steel or nylon fittings.

### Product Specifications

<b>Product Type</b>	Deluxe Cord Grips
<b>Thread Type</b>	N.P.T.
<b>Grip Style and Material</b>	Straight Aluminum Connector Stainless Grip
<b>Grip Cord Range (Diameter)</b>	1.937"- 2.062" (4.92- 5.24)
<b>Grip Thread Size</b>	2"
<b>Deluxe Grip Form Size</b>	F7
<b>Operating Temperature</b>	-30°F to +225°F (-34°C to +107°C)
<b>Mesh Grip Flammability Rating</b>	UL 94-HB
<b>Fitting Flammability Rating</b>	UL 94-V2
<b>Recommended Knockout Hole Size</b>	2.453 to 2.500 (6.23 - 6.35)
<b>Hazardous Locations</b>	Suitable for use in hazardous locations per Class I, Div. 2, Class II, Div. 1 & 2, Class III, Div. 1 & 2.
<b>Dimension A</b>	3.85" (9.78) Dia.
<b>Dimension B</b>	2.70" (6.86) Ref.
<b>Dimension C</b>	.88" (2.24)
<b>Dimension D</b>	1.94" (4.93) Throat Dia.
<b>Dimension E A/C</b>	4.05" (10.29)
<b>Dimension E A/F</b>	3.75" (9.52)
<b>Dimension F</b>	2" - 11 1/2
<b>Certifications</b>	UL Listed CSA Certified
<b>UPC Number</b>	78358533089
<b>Weight in LBs</b>	2.05
<b>Link to Drawing Library</b>	<a href="#">Click here for Library</a>
<b>Link to PDF Catalog</b>	<a href="#">Click here for Catalog</a>



