



**94063-12: 500w 24V Single Output Multi-Tap Transformer**



**Dimensions:**

**Length:** 9 1/2"  
**Width:** 5 3/8"  
**Height:** 4 3/4"

**Mounting Proc.:** Screw(s)

**Features:**

- Powder coat added to the finish to protect against aging.

**Material List:**

1 Transformer - Metal - Black

**Safety Listing:**

Safety Listed for Dry Locations  
 Safety Listed for Dry Locations

**Instruction Sheets:**

Bilingual (English - French) (HC-1815FB)

**Collections:** Hardwire Transformers (Primary)  
 Mini-Recessed Transformers

Magnetic transformers are encased in a powder coated metal enclosure that is potted to minimize noise and vibration. All are UL/cUL Listed, NEC 411 Approved, thermally protected, dimmable and have resettable magnetic circuit breakers for short circuit protection. Housings feature easy-hang bracket, wiring access door and knockouts for line voltage entry. Multi-tap transformers compensate for voltage drop on long secondary runs. (24, 26, 28, 30V)

Multi-Tap (24v) 24, 26,28,30 Volt

**UPC #:**785652940613

**Finish:** Black (12)

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	94063-12	1	785652940613	15	7	6	0.365	19.7	60	Yes
Shipping Master		2	10785652940610	15.75	14.25	7	0.909	41	60	Yes
NJ Pallet		72		48	40	46.5	51.667	1476		No
NV Pallet		65		48	40	52	57.778	1150.5		No