

Bells Vibrating 13 Series

Edwards 13 Series bells are compact in size and feature a sound that is suitable for a variety of applications, including offices, apartment houses, intercom and telephone signaling, as well as OEM uses. Models suitable for AC powered security systems are available.

Features and Specifications

- Chrome plate finish
- Adjustable volume
- 1", 2" and 3" gong sizes
- Grounded frame
- External binding posts



Ordering Information

Description	Cat. No.	Operating Voltage	Current	VA	Gong Size	dB at 1m/10ft.	DC Coil Res (Ohms)
AC	13-1G5	24V AC	0.20 A	4.8	1" (25mm)	74/64	85
	13-2G5	24V AC	0.25 A	6.0	2" (51mm)	75/65	56
	13-3G5	24V AC	0.25 A	6	3" (76mm)	77/67	30
DC	13-1G1	24V DC	0.20 A	4.8	1" (25mm)	74/64	120
	13-2G1	24V DC	0.25 A	6.0	2" (51mm)	75/65	90
	13-3G1	24V DC	0.25 A	6	3" (76mm)	77/67	44
AC/DC	13-1AB	5-10V DC	0.35 A	2.0	1" (25mm)	74/64	10
		6-12V AC	0.50 A	4.0			
	13-2AB	5-10V DC	0.40 A	2.5	2" (51mm)	75/65	8
		6-12V AC	0.50 A	4.0			
	13-3AB	5-10V DC	0.60 A	3.5	3" (76mm)	77/67	5
		6-12V AC	0.40 A	3.5			

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)	Dimensions			
			A	B	C	D
13-1AB	0.07	0.10	1 1/4" (32mm)	3/4" (19mm)	3 1/8" (79mm)	1 3/4" (44mm)
13-1G1	0.07	0.10	1 1/4" (32mm)	3/4" (19mm)	3 1/8" (79mm)	1 3/4" (44mm)
13-1G5	0.07	0.10	1 1/4" (32mm)	3/4" (19mm)	3 1/8" (79mm)	1 3/4" (44mm)
13-2AB	0.10	0.30	1 3/4" (44mm)	1 1/16" (27mm)	3 29/32" (99mm)	2 1/32" (52mm)
13-2G1	0.10	0.30	1 3/4" (44mm)	1 1/16" (27mm)	3 29/32" (99mm)	2 1/32" (52mm)
13-2G5	0.10	0.30	1 3/4" (44mm)	1 1/16" (27mm)	3 29/32" (99mm)	2 1/32" (52mm)
13-3AB	0.29	0.60	3" (76mm)	1 9/16" (40mm)	5 7/8" (149mm)	3 1/2" (89mm)
13-3G1	0.29	0.60	3" (76mm)	1 9/16" (40mm)	5 7/8" (149mm)	3 1/2" (89mm)
13-3G5	0.29	0.60	3" (76mm)	1 9/16" (40mm)	5 7/8" (149mm)	3 1/2" (89mm)

