

LIQUIDTIGHT

90 DEGREE CONDUIT AND CORD CONNECTORS - STEEL/MALLEABLE IRON

B48

Click on catalog number next to image to access individual product data sheet.

Applications

- For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Use to positively bond the conduit to a box or enclosure

3421
3421-8
3422
3422-8
3423
3423-8
3424
3424-8
3425
3426
3428
3430
3432
3436



3541RAC
3542
3542-8
3543
3543-8
3544
3544-8
3545
3546
3548
3550
3552
3556



Product Features

- RACO liquidtight connectors are suitable for use in Class I, Div. 2, Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations
- Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
- All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service
- Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
- Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
- All steel/iron components are zinc electro plated for added corrosion protection
- 3/8 in. to 4 in. Malleable iron bodies
- 3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts

Cat.	Sub Class	Trade Size	Package Type	Std. Pkg.	Ship Carton Qty.	Bar Code
90 Degree Connectors Steel/Malleable Iron						
3421	Uninsulated	3/8 in.	Carton	25	100	---
3421-8	Uninsulated	3/8 in.	Carton	1	15	
3422	Uninsulated	1/2 in.	Carton	25	100	---
3422-8	Uninsulated	1/2 in.	Carton	1	15	
3423	Uninsulated	3/4 in.	Carton	25	100	---
3423-8	Uninsulated	3/4 in.	Carton	1	10	
3424	Uninsulated	1 in.	Carton	N/A	10	---
3424-8	Uninsulated	1 in.	Carton	1	5	
3425	Uninsulated	1-1/4 in.	Carton	N/A	10	---
3426	Uninsulated	1-1/2 in.	Carton	N/A	5	---
3428	Uninsulated	2 in.	Carton	N/A	5	---
3430	Uninsulated	2-1/2 in.	Carton	N/A	1	---
3432	Uninsulated	3 in.	Carton	N/A	1	---
3436	Uninsulated	4 in.	Carton	N/A	1	---
3541RAC	Insulated	3/8 in.	Carton	25	100	---
3542	Insulated	1/2 in.	Carton	25	100	---
3542-8	Insulated	1/2 in.	Carton	1	15	
3543	Insulated	3/4 in.	Carton	25	100	---
3543-8	Insulated	3/4 in.	Carton	1	10	
3544	Insulated	1 in.	Carton	N/A	10	---
3544-8	Insulated	1 in.	Carton	1	5	
3545	Insulated	1-1/4 in.	Carton	N/A	10	---
3546	Insulated	1-1/2 in.	Carton	N/A	5	---
3548	Insulated	2 in.	Carton	N/A	5	---
3550	Insulated	2-1/2 in.	Carton	N/A	1	---
3552	Insulated	3 in.	Carton	N/A	1	---
3556	Insulated	4 in.	Carton	N/A	1	---

UL Listed

- Standard 514B, UL Listed E195969

CSA

- C22.2 No. 18

Compliances 3

- MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings,January_2015.pdf (/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings,January_2015.pdf)