

 Listed - File E27731

 Certified - File LR11851

VFC Fixture Bodies

Fixture bodies contain lamp receptacle and are threaded to accept globes, guards and reflectors. These fixture bodies are designed for metallic boxes and mount directly to V Series splice

boxes. They may also be mounted to VJ Series, VB Series or other 4" outlet boxes with the use of the appropriate adapter plate. Each fixture body is supplied with gaskets.



VFC-100
VXFC-100Ⓢ



VFC-200
VXFC-200Ⓢ

V FIXTURE BODIES	
CATALOG NUMBER	DESCRIPTION
VFC-100	150W max. Enclosed & Gasketed Fixture Body
VFC-200	300W max. Enclosed & Gasketed Fixture Body
VXFC-100 N34	150W max. NEMA 3,4 - Class I, Div. 2 Fixture BodyⓈ
VXFC-200 N34	300W max. NEMA 3,4 - Class I, Div. 2 Fixture BodyⓈ

Ⓢ Use VXFC body with tempered globe for NEMA 3, 4 - Class I, Div. 2 applications. VXFC body is Class I, Div. 2 only (not N3, N4) when used with standard globes. Consult temperature table, page L9 for suitability.



VGA



VGH



VGC



VGX



VXA



VBC

V Splice Boxes

For use with types 100 and 200 fixture bodies

V SPLICE BOXES		
CATALOG NUMBER	HUB SIZE & QTY.	DESCRIPTION
VGA-1	1/2" 1	Pendant mount
VGA-2	3/4" 1	
VGH-1	1/2" 1	Ceiling mount
VGH-2	3/4" 1	
VGC-1	1/2" 2	Ceiling mount
VGC-2	3/4" 2	
VGX-1	1/2" 4	Ceiling mount
VGX-2	3/4" 4	
VXA-1	1/2" 5	Ceiling mount, deep box
VXA-2	3/4" 5	
VBC-1*	1/2" 4	Ceiling mount, with 3 close-up plugs (requires VBA Adapter)
VBC-2*	3/4" 4	
VXAB	- -	Blank close-up plate (less gasket)

* Volume cu. in. is 18.



VBA



VFPS

V ADAPTER MOUNTING PLATES	
CATALOG NUMBER	DESCRIPTION
VBA	Adapts fixture body to VB, VJ or steel 3-1/2" & 4" splice boxes. Supplied with gasket.
VFPS	Adapts fixture body to steel 4" square outlet boxes or 3-1/2" or 4" octagon boxes



VB



VFL



VD

V MOUNTING BRACKETS			
CATALOG NUMBER	HUB SIZE	QTY.	DESCRIPTION
VB-1	1/2"	1	Wall mount to VJ or VB boxes
VB-2	3/4"	1	Wall mount to VJ or VB boxes
VFL	—	—	Wall mount to V boxes directly or to VJ, VB boxes with VBA adapter
VD-4	1-1/4"	1	Stanchion mount

