

DESCRIPTION

The CU2 Series offers quality and value with a compact and attractive LED based emergency light. The white or black housing and lamp-heads are made of high impact UL flame rated thermoplastic. Lamp-heads are fully adjustable and glare-free. Snap together design for quick and easy installation with option of Wall or Ceiling mount. Remote capacity unit will run a double-head remote or 2 single-head remotes of either the Compass CIR or COR Series.

APPLICATION

The CU2 Series can be applied in stair-wells, hallways, offices and other commercial applications.

COMPLIANCES

UL924 Listed for Damp Location
 NFPA 101 and NFPA 70
 OSHA

WARRANTY

2 year full unit warranty



FEATURES

- LED life-cycle of more than 10 years
- Quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Remote capacity or extended runtime option
- Damp Location Listed
- Fully adjustable lamp-heads
- Provided with test switch and AC-On indicator
- Wall or Ceiling mount

ENERGY CONSUMPTION


	120 VAC	277 VAC
CU2	.56 W	.54 W
CU2RC	.92 W	1.62 W

ORDERING GUIDE

Catalog Number	Description
CU2	White Thermoplastic, Dual-Head LED Emergency Light, 120/277 Input, Damp Location Listed, 3 VDC, 1 Watt
CU2B	Black Thermoplastic, Dual-Head LED Emergency Light, 120/277 Input, Damp Location Listed, 3 VDC, 1 Watt
CU2RC	White Thermoplastic, Dual-Head LED Emergency Light, 120/277 Input, Damp Location Listed, Remote Capacity, 3VDC, 1Watt
CU2RCB	Black Thermoplastic, Dual-Head LED Emergency Light, 120/277 Input, Damp Location Listed, Remote Capacity, 3VDC, 1Watt

Note: Remote Capacity Unit will only power the Compass Indoor and Outdoor Remote(CIR and COR Series)

DIMENSIONS



Single Carton Weight: 1 lbs.
Master Carton Quantity: 12 each

ACCESSORIES

WGLZ Wireguard - 6.25" H X 14" W X 4" D
 CIR Series - Matching LED Indoor Remote Heads
 COR Series - Matching LED Outdoor Remote Heads

