



MERCURY

BATH AND VANITY

Product ID: **1405-SN**

Available Finishes:

PC (Polished Chrome)

SN (Satin Nickel)



Swirl glass shows its finely brushed texture in the Mercury collection. Bands of shadowing give the glass bowls a soft, linen-like appearance when illuminated. Mercury juxtaposes square fixture bars with circular socket holders and backplates to create an appealing, well-balanced composition.

Dimensional Information

Height: 7"
 Length: 0"
 ADA Compliant: N
 Chain Length: 0"
 Stem Kit: N/A
 Canopy/Backplate: 4.5" D
 Width: 40.5"
 Diameter: 0"
 Minimum Height: 0"
 Maximum Height: 0"
 Extension: 6.5"

Lamping Information

(5) 75 Watt Max 120.000V

Bulb Included: Y

Socket Type: G9 Wedgebase

Shade Information

Shade Top: 5.75"
 Shade Bottom: 2"
 Shade Height: 7.375"
 Shade Attachment: Socket Ring
 Shade Material: Glass
 Shade Color: White Swirl

Shipping Information

Carton Length: 43"
 Carton Width: 10"
 Carton Height: 8"
 Gross Weight: 13lb.
 Shipping Method: UPS
 Quantity Per Carton: 1

