



NEWPORT

WALL SCONCE

Product ID: **1901-SN**

Available Finishes:

- AGB (Aged Brass)
- PN (Polished Nickel)
- SN (Satin Nickel)



We cast our Newport collection with the cherished heritage of handsome American style. Choose between the crisp-lined rectangular backplate, the smooth rounded backplate, and the Palladian-arched backplate, which features a shapely bracket mount for the candelabra lamp.

Dimensional Information

- Height: 12"
- Length: 0"
- ADA Compliant: N
- Chain Length: 0"
- Stem Kit: N/A
- Canopy/Backplate: 4.75" D
- Width: 5"
- Diameter: 0"
- Minimum Height: 0"
- Maximum Height: 0"
- Extension: 7.25"

Lamping Information

- (1) 60 Watt Max 120.000V
- Bulb Included: N
- Socket Type: E12 Candelabra

Shade Information

- Shade Top: 3"
- Shade Bottom: 5"
- Shade Height: 5"
- Shade Attachment: Clip
- Shade Material: Faux Silk
- Shade Color: Off White

Shipping Information

- Carton Length: 14"
- Carton Width: 10"
- Carton Height: 11"
- Gross Weight: 3lb.
- Shipping Method: UPS
- Quantity Per Carton: 1

