



**WINDHAM**

BATH AND VANITY  
 Product ID: **3403-PN**

**Available Finishes:**

- OB (Old Bronze)
- PN (Polished Nickel)
- SN (Satin Nickel)



Strong and handsome, the Windham collection showcases the timeless appeal of classical styling. Mouth-blown opal glass canisters mount to cast metal socket holders, replete with crisply turned steps and finely etched dentil knurling. Subtle knurling appears again on Windham’s circular backplate, reinforcing the classical motif.

**Dimensional Information**

Height: ..... 9.75"  
 Length: ..... 0"  
 ADA Compliant: ..... N  
 Chain Length: ..... 0"  
 Stem Kit: ..... N/A  
 Canopy/Backplate: ..... 5.25" D  
 Width: ..... 22.5"  
 Diameter: ..... 0"  
 Minimum Height: ..... 0"  
 Maximum Height: ..... 0"  
 Extension: ..... 6.25"

**Lamping Information**

(3) 100 Watt Max 120.000V  
 Bulb Included: ..... N  
 Socket Type: ..... E26 Medium Base

**Shade Information**

Shade Top: ..... 1.875"  
 Shade Bottom: ..... 4.75"  
 Shade Height: ..... 5.125"  
 Shade Attachment: ..... Socket Ring  
 Shade Material: ..... Glass  
 Shade Color: ..... Opal/Glossy

**Shipping Information**

Carton Length: ..... 23"  
 Carton Width: ..... 15"  
 Carton Height: ..... 9"  
 Gross Weight: ..... 9lb.  
 Shipping Method: ..... UPS  
 Quantity Per Carton: ..... 1

