



PORCELAIN

BATH AND VANITY

Product ID: **463-SN**

Available Finishes:

- PB (Polished Brass)
- PN (Polished Nickel)
- SN (Satin Nickel)



Glazed white porcelain is the choice material where cleanliness is crucial. A swift wipe removes all blemishes, leaving the bright white surface gleaming with unspoiled purity. We pair glazed porcelain accents with brass metalwork for a perpetually fresh look. Opal glass bells mimic the porcelain’s contour, while softly diffusing bulb glare.

Dimensional Information

- Height: 9.75"
- Length: 0"
- ADA Compliant: N
- Chain Length: 0"
- Stem Kit: N/A
- Canopy/Backplate: 5.25" D
- Width: 22.5"
- Diameter: 0"
- Minimum Height: 0"
- Maximum Height: 0"
- Extension: 8"

Lamping Information

- (3) 100 Watt Max 120.000V
- Bulb Included: N
- Socket Type: E26 Medium Base

Shade Information

- Shade Top: 6"
- Shade Bottom: 3.25"
- Shade Height: 4"
- Shade Attachment: Socket Ring
- Shade Material: Glass
- Shade Color: Opal/Matte

Shipping Information

- Carton Length: 29"
- Carton Width: 13"
- Carton Height: 11"
- Gross Weight: 8lb.
- Shipping Method: UPS
- Quantity Per Carton: 1

