



RICHMOND

BATH AND VANITY

Product ID: **4943-FB**

Available Finishes:

FB (Flemish Brass)

OB (Old Bronze)

PN (Polished Nickel)



The early electric period, when fixtures showed close kinship to the gas lamps they replaced, coincided with a revival of the architecture that predated the American Revolution. The dentil cornices that ring Richmond's shade tops evoke the trim-work of an 18th century Virginia manor house, while the vented glass and strong metal tubing are a legacy of the fixture's gas lamp predecessors.

Dimensional Information

Height: 7.5"
 Length: 0"
 ADA Compliant: N
 Chain Length: 0"
 Stem Kit: N/A
 Canopy/Backplate: 6.5" W X 4.75" H
 Width: 23.75"
 Diameter: 0"
 Minimum Height: 0"
 Maximum Height: 0"
 Extension: 6.75"

Lamping Information

(3) 75 Watt Max 120.000V

Bulb Included: Y

Socket Type: G9 Wedgebase

Shade Information

Shade Top: 1"
 Shade Bottom: 3.375"
 Shade Height: 4"
 Shade Attachment: Socket Ring
 Shade Material: Glass
 Shade Color: Opal/Glossy

Shipping Information

Carton Length: 22"
 Carton Width: 14"
 Carton Height: 8"
 Gross Weight: 8lb.
 Shipping Method: UPS
 Quantity Per Carton: 1

