

**CONTROL POWER
TRANSFORMERS**

Type MTE

VA	Dimensions (Inches)			Weight Lbs.	Dimensions (mm)			Weight kg	Wiring Diagram ①	Catalog Number	*
	H	W	D		H	W	D				

Primary: 240 x 480 with Jumpers

Secondary: 120 x 240 with Jumpers, Fuse Clips Not Applicable

50	2-9/16	3	3	2.6	65	76	76	1.2	11	C0050E2CXX	
75	2-9/16	3	3-1/2	3.5	65	76	89	1.6	11	C0075E2CXX	
100	2-7/8	3-3/8	3-3/8	4.2	73	86	86	1.9	11	C0100E2CXX	
150	3-3/16	3-3/4	4	6.7	81	95	102	3.1	11	C0150E2CXX	
200	3-13/16	4-1/2	4	8.5	97	114	102	3.9	11	C0200E2CXX	
250	3-13/16	4-1/2	4-3/8	10.0	97	114	111	4.6	11	C0250E2CXX	
300	3-13/16	4-1/2	4-7/8	11.8	97	114	124	5.4	11	C0300E2CXX	
350	3-13/16	4-1/2	5-1/4	13.6	97	114	133	6.2	11	C0350E2CXX	
500	4-3/4	5-1/4	5-1/4	17.5	121	133	133	8.0	11	C0500E2CXX	
750	4-3/4	5-1/4	7	26.4	121	133	178	12.0	11	C0750E2CXX	

Primary: 550/575/600

Secondary: 110/115/120 with Fuse Clips for 13/32 x 1-1/2 Fuses

50	2-9/16	3	3	2.7	65	76	76	1.2	10	C0050E4C	
75	2-9/16	3	3-1/2	3.6	65	76	89	1.6	10	C0075E4C	
100	2-7/8	3-3/8	3-3/8	4.2	73	86	86	1.9	10	C0100E4C	
150	3-3/16	3-3/4	4	6.8	81	95	102	3.1	10	C0150E4C	
200	3-13/16	4-1/2	4	8.4	97	114	102	3.8	10	C0200E4C	
250	3-13/16	4-1/2	4-3/8	10.0	97	114	111	4.6	10	C0250E4C	
300	3-13/16	4-1/2	4-3/4	11.3	97	114	121	5.1	10	C0300E4C	
350	3-13/16	4-1/2	5-1/4	13.6	97	114	133	6.2	10	C0350E4C	
500	4-3/4	5-1/4	5-3/8	16.8	121	133	137	7.6	10	C0500E4C	
750	4-3/4	5-1/4	7	25.7	121	133	178	11.7	10	C0750E4C	

Primary: 380/400/415

Secondary: 22/23/24 with Fuse Clips for 13/32 x 1-1/2 Fuses

50	2-9/16	3	3	2.5	65	76	76	1.1	13	C0050E4H	
75	2-9/16	3	3-1/2	3.5	65	76	89	1.6	13	C0075E4H	
100	2-7/8	3-3/8	3-3/8	4.0	73	86	86	1.8	13	C0100E4H	
150	3-3/16	3-3/4	4	6.5	81	95	102	3.0	13	C0150E4H	
200	3-13/16	4-1/2	4	8.2	97	114	102	3.7	13	C0200E4H	
250	3-13/16	4-1/2	4-3/8	10.0	97	114	111	4.5	13	C0250E4H	
300	3-13/16	4-1/2	4-3/4	11.0	97	114	121	5.0	13	C0300E4H	
350	3-13/16	4-1/2	5-1/4	13.6	97	114	133	6.2	13	C0350E4H	
500	4-3/4	5-1/4	5-1/2	17.7	121	133	140	8.0	13	C0500E4H	

Primary: 550/575/600

Secondary: 22/23/24 with Fuse Clips for 13/32 x 1-1/2 Fuses

50	2-9/16	3	3	2.5	65	76	76	1.1	12	C0050E4W	
75	2-9/16	3	3-1/2	3.5	65	76	89	1.6	12	C0075E4W	
100	2-7/8	3-3/8	3-3/8	4.0	73	86	86	1.8	12	C0100E4W	
150	3-3/16	3-3/4	4	6.5	81	95	102	3.0	12	C0150E4W	
200	3-13/16	4-1/2	4	8.2	97	114	102	3.7	12	C0200E4W	
250	3-13/16	4-1/2	4-3/8	10.0	97	114	111	4.5	12	C0250E4W	
300	3-13/16	4-1/2	4-3/4	11.0	97	114	121	5.0	12	C0300E4W	
350	3-13/16	4-1/2	5-1/4	13.6	97	114	133	6.2	12	C0350E4W	
500	4-3/4	5-1/4	5-1/2	17.7	121	133	140	8.0	12	C0500E4W	
750	4-1/2	5-1/4	7-3/8	28.0	114	133	187	12.7	12	C0750E4WXXX	

① See Pages 9-24 and 9-25 for Wiring Diagrams.

NOTE: For additional information, refer to Cutler-Hammer Industrial Control Transformer Binder B1228A.

*Prices — Consult Sales Office or Price List