

Catalog Number: 10-501
Product ID: 7TAA008620R0029
UPC Number: 78378610501
Status: Active

Crimp sleeve wire connector HI-411.

- Zinc plated, chromate treated steel.
- Two sizes accommodate #18-8 AWG stranded copper.

North American Specifications (UNSPSC)

UNSPSC	39121409 Wire connectors
IGCC	4543 Wire connectors
Brand Name	T&B
Type	Wire Connectors & Termination
Special Features	Zinc plated, chromate treated steel.
Standard	UL E9809, CSA 6591000
Wire Size	#18 - 10 Str
Material	Steel
Finish	Zinc Plated
Voltage Rating	300V

Packaging

Inner Quantity	50
Outer Quantity	500
Outer Dimensions (inches)	10.8x5.5x3.5
Weight Uom	3.75 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com