



## Grounding Block



### Features

- 2 port grounding block for F-Type connectors
- Solid zinc alloy, nickel plated and chromate finished
- High performance 360 degree beryllium copper contact
- Excellent performance 0 - 3000 MHz
- Dual Grounding holes can accept up to 6 awg wire
- UL / CSA approved

### Models

Description	Catalog #
Grounding Block	85-311