



Representative

**Catalog Number:** AL7  
**Product ID:** 7TAA268440R0010  
**UPC Number:** 78378604723  
**Status:** Active

Aluminum one-Hole Lug - Straight Long Barrel, Wire Range 2/0 ASCR, 2/0 Stranded, 3/0 Compact, 1/2 Inch Bolt Size, Blind-End, Mechanical Dies: 840, K840, 845, TX, Hydraulic Dies: 840, B49EA, EEI, 11A, K840, 249, 76, CSA 24

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Compression Connector
Special Features	PreFilled with Compound. Complete Die and Crimp information clearly indented on each lug. Installed with standard tools and dies. Use 1/2 inch mounting hardware for all sizes.
Application	For Aluminum and Copper Conductor.
Cable Size	2/0 ASCR, 2/0 Stranded, 3/0 Compact
Number Of Holes	2
Material	Aluminum
Mounting	NEMA Standard Mounting Holes
Connection	Crimp

### European Specifications (ETIM)

ETIM	EC001053 Crimp cable lug for aluminium conductors
Material	Aluminium
Number of fixing holes	1
Sleeve form	Long

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	7.13x6.13x4.81
Outer Quantity	100
Outer Dimensions (inches)	21x11.25x7.88
Weight Uom	21.63 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)