



Appliance Rocker Switches



Features

- Great for home appliances, computer equipment, automotive and industrial controls
- Appliance Rockers fit standard .55 in. - 1.12 in. panel cut outs
- Miniature Rockers fit .520 in. - .776 in. panel cut outs
- Plain and lighted versions available
- Operating temperature: 32°F to 185°F (0°C to 85°C)
- Bulk packaging of 100 available upon request

Models

Description	Rocker	Poles	Circuitry	Termination	Cat. No.
Appliance Rocker Switch	Black	SPST	On-Off	Spade	774038*
Appliance Rocker Switch	Red Lighted	SPST	On-Off	Spade	774039**
Appliance Rocker Switch	Visi-Red Rocker Printed On-Off Vertical	SPST	On-Off	Spade	774047**
Appliance Rocker Switch	Visi-Red Rocker	SPST	On-Off	Spade	774052+
Appliance Rocker Switch	Red Lighted	SPST	On-Off	Spade	774048++

* 16 Amp 125VAC/VCA, 8 Amp 250VAC/VCA, 1 HP 125-250VAC/VCA

** 20 Amp 125VAC/VCA, 10 Amp 250VAC/VCA, 1 1/2 HP 125-250VAC/VCA