

# IDEAL® TOOLS & SUPPLIES

## Valu-Line™ Pull-Line

- White with gray tracer for easy identification
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use



Description	Tensile Strength	Cat. No.
Valu-Line™ Pull-Line – 6,500 ft. (bucket)	190 lbs.	<b>31-338</b>

## Powr-Fish® Pull-Line

- White with blue tracer for easy identification
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use



Description	Tensile Strength	Cat. No.
Powr-Fish® Pull-Line – 6,500 ft. (bucket)	210 lbs.	<b>31-340</b>
Powr-Fish® Pull-Line – 500 ft. (canister)	210 lbs.	<b>31-348</b>

## Powr-Fish® Pull-Line

- White with red tracer for easy identification
- 500 lb. tensile, our highest tensile-rated pull-line
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use



Description	Tensile Strength	Cat. No.
Powr-Fish® Pull-Line – 2,200 ft. (bucket)	500 lbs.	<b>31-344</b>

## Pro-Pull™ Rope

- Low-friction polypropylene rope slides easily through conduit
- Non-sliver surface can be handled without gloves
- Will not rot or mildew
- Rugged, lightweight construction



Description	Tensile Strength	Cat. No.
1/4 in. x 250 ft. Reel	1,125 lbs.	<b>31-839</b>
1/4 in. x 600 ft. Reel	1,125 lbs.	<b>31-840</b>
1/4 in. x 1,000 ft. Reel	1,125 lbs.	<b>31-841</b>
3/8 in. x 250 ft. Reel†	2,430 lbs.	<b>31-844</b>
3/8 in. x 600 ft. Reel†	2,430 lbs.	<b>31-845</b>
3/8 in. x 1,200 ft. Reel†	2,430 lbs.	<b>31-846</b>
1/2 in. x 250 ft. Reel†	3,780 lbs.	<b>31-849</b>
1/2 in. x 600 ft. Reel†	3,780 lbs.	<b>31-850</b>
1/2 in. x 1,200 ft. Reel†	3,780 lbs.	<b>31-851</b>
5/8 in. x 600 ft. Reel†	5,580 lbs.	<b>31-853</b>
5/8 in. x 1,200 ft. Reel†	5,580 lbs.	<b>31-854</b>
3/4 in. x 300 ft. Reel†	7,650 lbs.	<b>31-855</b>
3/4 in. x 600 ft. Reel†	7,650 lbs.	<b>31-856</b>
3/4 in. x 1,200 ft. Reel†	7,650 lbs.	<b>31-857</b>

† Eye splice on working end.

## 3-in-1 Premise MULETAPE®

- Reduces installation time and saves money on premise jobs
- Thread, measure and pull with single product
- Imprinted with sequential footage or meter markings
- Fewer installation steps, significant material and labor savings



**THREE functions in ONE**

Description	Pulling Strength	Tape Width	Length	Cat. No.
3-in-1 Premise MULETAPE® 	400 lb.	1/4 in.	4,500 ft./ bucket	<b>31-314</b>
	1,800 lb.	1/2 in.	1,300 ft./ bucket	<b>31-315</b>

MULETAPE® is a registered trademark of NEPTCO.