

IDEAL[®] TOOLS & SUPPLIES

Valu-Line™ Pull-Line

- White with gray tracer for easy identification
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use

STANDARD Duty



| Description | Tensile Strength | Cat. No. |
|---|------------------|---------------|
| Valu-Line™ Pull-Line – 6,500 ft. (bucket) | 190 lbs. | 31-338 |

Powr-Fish® Pull-Line

- White with blue tracer for easy identification
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use

HEAVY Duty



| Description | Tensile Strength | Cat. No. |
|---|------------------|---------------|
| Powr-Fish® Pull-Line – 6,500 ft. (bucket) | 210 lbs. | 31-340 |
| Powr-Fish® Pull-Line – 500 ft. (canister) | 210 lbs. | 31-348 |

Powr-Fish® Pull-Line

- White with red tracer for easy identification
- 500 lb. tensile, our highest tensile-rated pull-line
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use

EXTRA-HEAVY Duty 500#



| Description | Tensile Strength | Cat. No. |
|---|------------------|---------------|
| Powr-Fish® Pull-Line – 2,200 ft. (bucket) | 500 lbs. | 31-344 |

Pro-Pull™ Rope

- Low-friction polypropylene rope slides easily through conduit
- Non-sliver surface can be handled without gloves
- Will not rot or mildew
- Rugged, lightweight construction



| Description | Tensile Strength | Cat. No. |
|---------------------------|------------------|---------------|
| 1/4 in. x 250 ft. Reel | 1,125 lbs. | 31-839 |
| 1/4 in. x 600 ft. Reel | 1,125 lbs. | 31-840 |
| 1/4 in. x 1,000 ft. Reel | 1,125 lbs. | 31-841 |
| 3/8 in. x 250 ft. Reel† | 2,430 lbs. | 31-844 |
| 3/8 in. x 600 ft. Reel† | 2,430 lbs. | 31-845 |
| 3/8 in. x 1,200 ft. Reel† | 2,430 lbs. | 31-846 |
| 1/2 in. x 250 ft. Reel† | 3,780 lbs. | 31-849 |
| 1/2 in. x 600 ft. Reel† | 3,780 lbs. | 31-850 |
| 1/2 in. x 1,200 ft. Reel† | 3,780 lbs. | 31-851 |
| 5/8 in. x 600 ft. Reel† | 5,580 lbs. | 31-853 |
| 5/8 in. x 1,200 ft. Reel† | 5,580 lbs. | 31-854 |
| 3/4 in. x 300 ft. Reel† | 7,650 lbs. | 31-855 |
| 3/4 in. x 600 ft. Reel† | 7,650 lbs. | 31-856 |
| 3/4 in. x 1,200 ft. Reel† | 7,650 lbs. | 31-857 |

† Eye splice on working end.

3-in-1 Premise MULETAPE®

- Reduces installation time and saves money on premise jobs
- Thread, measure and pull with single product
- Imprinted with sequential footage or meter markings
- Fewer installation steps, significant material and labor savings



| Description | Pulling Strength | Tape Width | Length | Cat. No. |
|---|------------------|------------|-------------------|---------------|
| 3-in-1 Premise MULETAPE®  | 400 lb. | 1/4 in. | 4,500 ft./ bucket | 31-314 |
| | 1,800 lb. | 1/2 in. | 1,300 ft./ bucket | 31-315 |

MULETAPE® is a registered trademark of NEPTCO.