



# TOOLS & SUPPLIES



### Phillips



### Square



### Cabinet

## Phillips

- Vapor-blasted tip prevents plate chipping
- Easy-to-read FastFinder™ handle shows tip type on end of handle
- Nickel Chrome plating for corrosion resistance
- Tough, chrome vanadium steel shank with cushioned-grip handle



Description	Blade Length	Handle Length	Overall Length	Cat. No.
#1 Phillips	3 in.	3-3/4 in.	6-3/4 in.	<b>35-193</b>
#2 Phillips	1-1/2 in.	1-15/16 in.	3-7/16 in.	<b>35-191</b>
#2 Phillips	4 in.	4-5/16 in.	8-5/16 in.	<b>35-194</b>
#2 Phillips	6 in.	4-5/16 in.	10-5/16 in.	<b>35-195</b>
#3 Phillips	6 in.	5-23/64 in.	11-23/64 in.	<b>35-196</b>

## Square

- Precise tip for square-recess screws
- Easy-to-read FastFinder™ handle shows tip type on end of handle
- Nickel Chrome plating for corrosion resistance
- Tough, chrome vanadium steel shank with cushioned-grip handle



Description	Blade Length	Handle Length	Overall Length	Cat. No.
#0 Square	4 in.	4-5/16 in.	8-5/16 in.	<b>35-690</b>
#1 Square	4 in.	4-5/16 in.	8-5/16 in.	<b>35-691</b>
#1 Square	8 in.	4-5/16 in.	12-5/16 in.	<b>35-692</b>
#2 Square	4 in.	4-5/16 in.	8-5/16 in.	<b>35-693</b>
#2 Square	8 in.	4-5/16 in.	12-5/16 in.	<b>35-694</b>
#3 Square	4 in.	4-5/16 in.	8-5/16 in.	<b>35-695</b>
#3 Square	8 in.	4-5/16 in.	12-5/16 in.	<b>35-696</b>

## Cabinet

- Vapor-blasted tip prevents plate chipping
- Easy-to-read FastFinder™ handle shows tip type on end of handle
- Precision ground tip provides secure fit in screw slot
- Nickel Chrome plating for corrosion resistance
- Tough, vanadium steel shank with cushioned-grip handle



Description	Blade Length	Handle Length	Overall Length	Cat. No.
3/16 in. shank and tip	3 in.	3-3/4 in.	6-3/4 in.	<b>35-183</b>
3/16 in. shank and tip	4 in.	3-3/4 in.	7-3/4 in.	<b>35-184</b>
3/16 in. shank and tip	6 in.	3-3/4 in.	9-3/4 in.	<b>35-186</b>
3/16 in. shank and tip	8 in.	3-3/4 in.	11-3/4 in.	<b>35-188</b>
3/16 in. shank and tip	10 in.	3-3/4 in.	13-3/4 in.	<b>35-190</b>

## Heavy-Duty Cabinet

- Large diameter shank for tough applications
- Easy-to-read FastFinder™ handle shows tip type on end of handle
- Vapor-blasted tip prevents plate chipping
- Precision ground tip provides secure fit in screw slot
- Nickel Chrome plating for corrosion resistance
- Tough, chrome vanadium steel shank with cushioned-grip handle



Description	Blade Length	Handle Length	Overall Length	Cat. No.
1/4 in. shank and tip	4 in.	4-5/16 in.	8-3/8 in.	<b>35-150</b>
1/4 in. shank and tip	6 in.	4-5/16 in.	10-3/8 in.	<b>35-151</b>
1/4 in. shank and tip	8 in.	4-5/16 in.	12-3/8 in.	<b>35-152</b>