






Nylon Fully-Insulated Female Disconnects

| Wire Range | Tab Size In. | Max. Wire Ins. Dia. In. | Qty. | Cat. No. | Qty. | Cat. No. |
|--|------------------------------|-------------------------|------|----------------|-------|----------------|
| 22 – 18 AWG (0,5-1,0mm ²)  | .250 x .032 (6.35mm x 0.8mm) | 0.15 (3.8mm) | 25 | 83-9771 | 1,000 | 84-9771 |
| 16 – 14 AWG (1,5-2,5mm ²)  | .250 x .032 (6.35mm x 0.8mm) | 0.185 (4.7mm) | 25 | 83-9781 | 1,000 | 84-9781 |
| 12 – 10 AWG (4,0-6,0mm ²)  | .250 x .032 (6.35mm x 0.8mm) | 0.244 (6.2mm) | 25 | 83-9791 | 500 | 84-9791 |


105° C/300 Volts max.

Vinyl Fully-Insulated Receptacle Disconnects

| Wire Range | Max. Wire Ins. Dia. In. | Quantity | Cat. No. |
|--|-------------------------|----------|----------------|
| 22 – 18 AWG (0,5-1,0mm ²)  | 0.150 (3.8mm) | 25 | 83-8101 |
| 16 – 14 AWG (1,5-2,5mm ²)  | 0.185 (4.7mm) | 25 | 83-8111 |

75° C/300 Volts max.

Non-Insulated Flag Female Disconnect*

| Wire Range | Tab Size In. | Quantity | Cat. No. |
|--|----------------------------|----------|----------------|
| 16 – 14 AWG (1,5-2,5mm ²)  | .250 x .032 (6.35 x 0.8mm) | 25 | 83-9401 |

105° C/300 Volts max.

Disconnect Adapter - Male to Female (2-1)*

| Tab Size (In.) | Quantity | Cat. No. |
|---|----------|----------------|
| .250 x .032 (6.35mm x 0.8mm)  | 25 | 83-9801 |

105° C/300 Volts max.

Non-Insulated Parallel Splices*

| Wire Range | Qty. | Cat. No. | Qty. | Cat. No. |
|---------------------------------------|------|----------------|-------|----------------|
| 22 – 18 AWG (0,5-1,0mm ²) | 25 | 83-9071 | — | — |
| 16 – 14 AWG (1,5-2,5mm ²) | 25 | 83-9081 | 1,000 | 84-9081 |
| 12 – 10 (4,0-6,0mm ²) | 25 | 83-9091 | 1,000 | 84-9091 |

105° C/600 Volts max.

*Not UL Listed

1-800-435-0705 CUSTOMER ASSISTANCE




Non-Insulated Butt Splices*



| Wire Range | Qty. | Cat. No. | Qty. | Cat. No. |
|---------------------------------------|------|----------------|-------|----------------|
| 22 – 18 AWG (0,5-1,0mm ²) | 25 | 83-9001 | — | — |
| 16 – 14 AWG (1,5-2,5mm ²) | 25 | 83-9011 | 1,000 | 84-9011 |
| 12 – 10 (4,0-6,0mm ²) | 25 | 83-9021 | 500 | 84-9021 |
| 8 (8,0mm ²) | 25 | 83-9031 | 250 | 84-9031 |
| 6 (14,0mm ²) | 20 | 83-9041 | — | — |
| 4 (22,0mm ²) | 20 | 83-9051 | — | — |




105° C/600 Volts max.

Vinyl Insulated Butt Splices

| Wire Range | Max. Wire Ins. Dia. In. | Qty. | Cat. No. | Qty. | Cat. No. |
|---|-------------------------|------|----------------|-------|----------------|
| 22 – 18 AWG (0,5-1,0mm ²)  | .157 (4.0mm) | 25 | 83-9281 | 1,000 | 84-9281 |
| 16 – 14 AWG (1,5-2,5mm ²)  | .177 (4.5mm) | 25 | 83-9291 | 1,000 | 84-9291 |
| 12 – 10 (4,0-6,0mm ²)  | .248 (6.3mm) | 25 | 83-9301 | 500 | 84-9301 |

75° C/600 Volts max.

Vinyl Insulated Parallel Splices

| Wire Range | Max. Wire Ins. Dia. In. | Qty. | Cat. No. |
|--|-------------------------|-------|----------------|
| 22 – 18 AWG (0,5-1,0mm ²)  | .157 (4.0mm) | 1,000 | 83-9351 |
| 16 – 14 AWG (1,5-2,5mm ²)  | .177 (4.5mm) | 1,000 | 83-9361 |
| 12 – 10 (4,0-6,0mm ²)  | .248 (6.3mm) | 500 | 83-9371 |

75° C/600 Volts max.

Tap Splice Connectors

| Wire Range | Color | Quantity | Cat. No. |
|---|--------|----------|----------------|
| 22 – 18 AWG (0,5-1,0mm ²)  | Red | 25 | 83-3261 |
| 16 – 14 AWG (1,5-2,5mm ²)  | Blue | 25 | 83-3271 |
| 12 – 10 (4,0-6,0mm ²)  | Yellow | 25 | 83-3281 |

75° C/600 Volts max.



WWW.IDEALINDUSTRIES.COM