



### Nylon Fully-Insulated Female Disconnects

Wire Range (AWG)	Wire Range (mm <sup>2</sup> )	Tab Size (Inches)	Tab Size (mm)	Max. Wire Ins. Dia. (Inches)	Max. Wire Ins. Dia. (mm)	Dimensions (Inches)				Dimensions (mm)				Ctn. Qty.	Cat. No.	Ctn. Qty.	Cat. No.
						L	B	W	F	L	B	W	L				
22 - 18	0.5 - 1.0	.250 x .032	6.35 x 0.8	.150	3.8	.866	.433	.260	.287	22.0	11.0	6.6	7.3	25	<b>83-9771</b>	—	—
16 - 14	1.5 - 2.5	.250 x .032	6.35 x 0.8	.185	4.7	.866	.433	.260	.287	22.0	11.0	6.6	7.3	25	<b>83-9781</b>	1,000	<b>84-9781</b>
12 - 10	4.0 - 6.0	.250 x .032	6.35 x 0.8	.244	6.2	.945	.512	.260	.287	24.0	13.0	6.6	7.3	25	<b>83-9791</b>	500	<b>84-9791</b>

105° C/300 Volts max.

Listed **774A** **Cu Only** **c** **Pressure Wire Connector**



### Nylon Fully-Insulated Male Disconnects

Wire Range (AWG)	Wire Range (mm <sup>2</sup> )	Tab Size (Inches)	Tab Size (mm)	Max. Wire Ins. Dia. (Inches)	Max. Wire Ins. Dia. (mm)	Dimensions (Inches)				Dimensions (mm)				Ctn. Qty.	Cat. No.
						L	B	W	F	L	B	W	F		
22 - 18	0.5 - 1.0	.250 x .032	6.35 x 0.8	.150	3.8	.906	.433	.250	.303	23.0	11.0	6.35	7.7	25	<b>83-9911</b>
16 - 14	1.5 - 2.5	.250 x .032	6.35 x 0.8	.185	4.7	.945	.433	.250	.303	24.0	11.0	6.35	7.7	25	<b>83-9921</b>
12 - 10	4.0 - 6.0	.250 x .032	6.35 x 0.8	.244	6.2	.984	.512	.250	.303	25.0	13.0	6.35	7.7	25	<b>83-9931</b>

105° C/300 Volts max.

Listed **774A** **Cu Only** **c** **Pressure Wire Connector**

### Vinyl Insulated Bullet Disconnects



Wire Range (AWG)	Wire Range (mm <sup>2</sup> )	Max. Wire Ins. Dia. (Inches)	Max. Wire Ins. Dia. (mm)	Dimensions (Inches)				Dimensions (mm)				Ctn. Qty.	Cat. No.
				L	B	W	F	L	B	W	F		
22 - 18	0.5 - 1.0	.150	3.8	.846	.413	.157	.335	21.5	10.5	4.0	8.5	25	<b>83-8001</b>
16 - 14	1.5 - 2.5	.185	4.7	.846	.413	.157	.335	21.5	10.5	4.0	8.5	25	<b>83-8011</b>

75° C/300 Volts max.

Listed **774A** **Cu Only** **c** **Pressure Wire Connector**

### Vinyl Fully-Insulated Receptacle Disconnects



Wire Range (AWG)	Wire Range (mm <sup>2</sup> )	Max. Wire Ins. Dia. (Inches)	Max. Wire Ins. Dia. (mm)	Dimensions (Inches)				Dimensions (mm)				Ctn. Qty.	Cat. No.
				L	B	W	F	L	B	W	F		
22 - 18	0.5 - 1.0	.150	3.8	.917	.413	.153	.287	23.3	10.5	3.9	7.3	25	<b>83-8101</b>
16 - 14	1.5 - 2.5	.185	4.7	.917	.413	.153	.287	23.3	10.5	3.9	7.3	25	<b>83-8111</b>

75° C/300 Volts max.

Listed **774A** **Cu Only** **c** **Pressure Wire Connector**