


89-400 Series Terminal Strips 20A/250V UL/CSA

- .437 in. (11.10mm) center spacing
- Accepts wire sizes from 22 through 12 AWG Cu
- #6-32 phillslot, zinc-plated steel terminal screws (Recommended torque: 9 in. - lb.)




No. of Poles	Dimensions (Inches)		Cat. No.
	A	B	
2	1.63	1.31	89-402
4	2.51	2.18	89-404
6	3.38	3.06	89-406
8	4.25	3.93	89-408
10	5.13	4.81	89-410
12	6.00	5.68	89-412




89-500 Series Terminal Strips 60A/600V* UL/CSA



- Available in standard or shorting-block style
- .625 in. (15.88mm) center spacing
- Accepts wire sizes from 22 through 6 AWG Cu
- #10-32 slotted, nickel plated brass terminal screws (Recommended torque: 20 in. - lb.)



Standard Block



Shorting Block



No. of Poles	Dimensions (Inches)		Standard Block Cat. No.	Shorting Block Cat. No.
	A	B		
4	3.75	2.87	89-504	89-505
6	5.00	4.12	89-506	89-507
8	6.25	5.37	89-508	89-509
12	8.75	7.87	89-512	89-513

*Max. electrical rating 60A/600V achieved only when used with #6 AWG copper wire crimped to ring terminal.

