

Split-Jaw™ Smart Meter

- Measures 0.9-200AAC
- Measures 1.3-750VAC
- Measures 2.1-1000VDC
- Measures 0.0-9999Ω
- Audible continuity
- Data hold
- Integral lead storage
- Replaceable test leads
- Auto power off
- Low battery indication
- 2-year warranty



Specifications

61-096		
AC Voltage	1.3 - 750 V	1.5%
DC Voltage	1.8 - 1000 V -0.6 - 1000 V	1.0%
AC Current	0.6 - 200.0A	3.0%
Resistance	0 - 2000 Ω	1.0%

*Note: Jaw opening is 0.6 in. (16mm) - up to 1/0 copper cable.

Description	Cat. No.
Split-Jaw™ Smart Meter	61-096

Includes: Test Leads.

Circuit Breaker Finders

- Fully automatic operation
- Positively identifies circuit breakers and fuses without service interruption
- Self calibrating
- Visual and audible indicators
- 2-year warranty



61-534
w/GFCI receptacle tester

TL-532A

61-532



Description	Cat. No.
Circuit Breaker Finder w/Digital Receiver & GFCI Circuit Tester	61-534
Circuit Breaker Finder w/Analog Receiver	61-532



Alligator clip adapter allows connections to exposed wiring.



Lighting adapter allows connection to light fixtures.

Specifications

	61-532	61-534
Operating Voltage	100 - 140 VAC	100 - 250 VAC
Operating Frequency	47 - 63 Hz	47 - 63 Hz