

Aqua-Gel® IIP Cable Pulling Lubricant

- Features the same excellent qualities as Aqua-Gel® II Cable Pulling Lubricant with a lower viscosity for easy pouring and pumping
- Pourable formula clings to cable – eliminates hand application for a cleaner and safer job
- Compatible with all cable types
- Cleans up easily with soap and water
- Environmentally safe – non-toxic, non-flammable and non-corrosive

| Description | Cat. No. |
|---------------|----------|
| 1-gal. Jug | 31-421 |
| 5-gal. Bucket | 31-425 |
| 55-gal. Drum | 31-435 |



Aqua-Gel® CW Cable Pulling Lubricant

- Features the same excellent qualities as Aqua-Gel® II Cable Pulling Lubricant with a lower temperature range for use outdoors in cold weather
- Polymer-based, cold-weather formula remains stable in storage from -28°F to 190°F (-33°C to 82°C)
- Formulated for exterior use in cold weather conditions
- Cleans up easily with soap and water
- Clings to cable throughout long pulls
- Well-suited for hand or poured applications
- Environmentally safe – non-toxic, non-flammable and non-corrosive

| Description | Cat. No. |
|----------------------|----------|
| 1-qt. Squeeze bottle | 31-298 |
| 1-gal. Jug | 31-291 |
| 5-gal. Bucket | 31-295 |
| 55-gal. Drum | 31-3373 |



Aqua-Gel® II Cable Pulling Lubricant

- Polymer-based formula provides maximum tension reduction in high-stress electrical and communications cable-pulling operations
- Compatible with all cable types except composite rubber
- Cleans up easily with soap and water
- Clings to cable throughout long pulls
- Remains stable over wide temperature range – usable from 28°F to 180°F (-2°C to 88°C)
- Dries to a semi-fluid film that won't clog conduit
- Easy to apply by hand, brush or pump
- Environmentally safe – non-toxic, non-flammable and non-corrosive
- For outdoor use only

| Description | Cat. No. |
|----------------------------------|----------|
| 1-qt. Squeeze bottle | 31-378 |
| 1-gal. Bucket | 31-371 |
| 1-qt. Bag (12 bags per bucket) | 31-376 |
| 1/2-gal. Bag (6 bags per bucket) | 31-377 |
| 5-gal. Bucket | 31-375 |
| 55-gal. Drum | 31-3855 |

