

## Nutmaster® Nutdrivers



- Long, hollow shank accommodates longer bolts
- Easy-to-read FastFinder™ handle shows tip type on end of handle
- Nickel Chrome plated to resist rust and corrosion
- Cushioned grips
- Models 35-292 and 35-295 fit Tan & Blue Twister® Wire Connectors



Description	Shank Length	Handle Length	Overall Length	Cat. No.
3/16 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-290</b>
1/4 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-291</b>
5/16 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-292</b>
11/32 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-293</b>

Description	Shank Length	Handle Length	Overall Length	Cat. No.
3/8 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-294</b>
7/16 in. x 4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-295</b>
1/2 in. x 4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-296</b>

## 7-Piece Nutdriver Set



Description				Cat. No.
7-Piece Nutdriver Set				<b>35-299</b>
35-299 Includes	Shank Length	Handle Length	Overall Length	Cat. No.
3/16 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-290</b>
1/4 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-291</b>
5/16 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-292</b>
11/32 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-293</b>
3/8 in. x 3-1/4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-294</b>
7/16 in. x 4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-295</b>
1/2 in. x 4 in.	3 in.	4-5/16 in.	7-5/16 in.	<b>35-296</b>

## 2-Piece Hollow-Shaft Nutdriver Set



- Includes 1/4 in. & 5/16 in.
- Long, hollow shank accommodates longer bolts
- Nickel Chrome plated to resist rust and corrosion
- Long shanks useful in deep electrical boxes



Description	Shank Length	Handle Length	Overall Length	Cat. No.
2-Piece Nutdriver Set	5-15/16 in.	4-5/16 in.	10-1/4 in.	<b>35-1302</b>

## 2-Piece Stubby Nutdriver Set

- Includes 1/4 in. & 5/16 in.
- For use in tight spaces



Description	Blade Length	Handle Length	Overall Length	Cat. No.
2-Piece Nutdriver Set	1-1/2 in.	2-1/8 in.	3-5/8 in.	<b>35-1299</b>