




## Side-Cutting Pliers

- Drop-forged, high-carbon steel construction withstands toughest applications
- Knife-to-anvil blades never need resharpening
- Cuts hardened wire, bolts and ACSR
- Laser-hardened blades and serrated jaws for long-term durability
- High-leverage design provides 40% more cutting power
- Unique reverse rivet protects smooth action of plier movement
- Vinyl-coated, comfort-grip handles for a secure grip



Description (Smart-Grip™ Plier Handles)	Cat. No.
9-1/4 in. New England nose high-leverage w/fish tape puller 	<b>35-3012</b>
9-1/4 in. New England nose high-leverage w/crimping die 	<b>30-3430</b>
Description (Dipped Handles)	Cat. No.
9-1/4 in. New England nose high-leverage w/fish tape puller 	<b>35-012</b>
9-1/4 in. New England nose high-leverage w/crimping die	<b>30-430</b>

## Long-Nose Pliers

- Narrow profile head designed for working in tight areas
- Serrated jaws provide secure gripping surface
- Drop-forged, high-carbon steel construction
- Knife-to-anvil blades never need resharpening
- Laser-hardened blades cut hardened wire, bolts and ACSR
- Vinyl-coated, comfort-grip handles for a secure grip



Description (Smart-Grip™ Plier Handles)	Cat. No.
8-1/2 in. Long Nose w/Cutter 	<b>35-3038</b>
Description (Dipped Handles)	Cat. No.
6 in. Long Nose w/Cutter	<b>35-036</b>
7-3/4 in. Long Nose w/Cutter	<b>35-037</b>
8-1/2 in. Long Nose w/Cutter	<b>35-038</b>
8-1/2 in. w/Cutter & stripping holes for 12 & 14 AWG wire 	<b>35-039</b>

## Tongue & Groove Pliers

- Reinforced flange protects against breakage
- Drop-forged, high-carbon steel construction
- Vinyl-coated, comfort-grip handles for a secure grip



Description (Smart-Grip™ Plier Handles)	Jaw Opening (Inches)	Cat. No.
10 in. Tongue & Groove Pliers 	2	<b>35-3430</b>
Description (Dipped Handles)	Jaw Opening (Inches)	(Inches)
10 in. Tongue & Groove Pliers 	2	<b>35-430</b>
12 in. Tongue & Groove Pliers 	2-1/4	<b>35-440</b>

## Cable Cutters

- Drop-forged, high-carbon steel construction
- Precision-ground, hardened cutting edges provide accurate cuts without cable distortion
- Designed for maximum leverage with minimum effort
- Cuts 2/0 copper and 4/0 aluminum (not for use on ACSR)
- Vinyl-coated, comfort-grip handles



Description (Smart-Grip™ Plier Handles)	Cat. No.
9-1/2 in. Cable Cutter 	<b>35-3052</b>
Description (Dipped Handles)	Cat. No.
9-1/2 in. Cable Cutter 	<b>35-052</b>



Side-Cutting



Long Nose