

Tungsten Carbide Grit Hole Saws

- Superior resistance to heat, wear and abrasion
- Unique snag resistant tooth/gullet design results in superior cutting performance
- The choice for abrasive or thin material including cast iron, drywall, plaster, stucco, ceramics, fiberglass, hardwood and composites
- 1-1/2 in. cutting depth



Diameter	Pipe Tap	Pipe Entrance	Cat. No.
Use Arbor No. 35-391, 35-392 or 35-393			
3/4 in.	1/2 in.	3/8 in.	35-343CG
7/8 in.	3/4 in.	1/2 in.	35-345CG
1-1/8 in.	1 in.	3/4 in.	35-349CG
Use Arbor No. 35-394, 35-536 or 35-537			
1-3/8 in.	—	1 in.	35-353CG
1-1/2 in.	1-1/4 in.	—	35-355CG
1-3/4 in.	1-1/2 in.	1-1/4 in.	35-359CG
2 in.	—	1-1/2 in.	35-362CG
2-1/8 in.	—	—	35-364CG
2-1/4 in.	2 in.	—	35-365CG
2-1/2 in.	—	2 in.	35-368CG
2-5/8 in.	2-1/2 in.	—	35-370CG
3 in.	—	2-1/2 in.	35-373CG
3-1/4 in.	3 in.	—	35-375CG
3-5/8 in.	—	3 in.	35-378CG

Adjustable Can Light Hole Saws

- Cuts drywall and ceiling tile
- Self-sharpening carbide coated cutting blades
- Includes 2 dust shields to minimize clean up



Drill not included.

Description	Cat. No.
Adjustable Can Light Hole Saw – 10 sizes from 2-1/2 in. to 7 in.	35-598
Adjustable Can Light Hole Saw – 13 sizes from 6-1/4 in. to 10-3/8 in.	35-599

Recessed Lighting Hole Saws

- Durable tungsten carbide grit cutting edge
- Quick and easy installation of recessed lighting
- Cut abrasive materials such as ceiling tile, lath and plaster
- Use with arbor 35-394



Diameter	For Fixtures	Cat. No.
4-3/8 in.	Capri®, Marco & Halo®, Mini-Juno®	35-384CG
6-3/8 in.	Capri®, Halo®, Pathway & Thomas	35-601CG
6-5/8 in.	Juno®, Progress & Pathway	35-602CG
6-7/8 in.	Capri®, Hubbell, Lightolier, Lithonia®, Prescolite, Progress	35-603CG