

## Stripmaster® and Stripmaster® Lite Wire Strippers

- One-step stripping enhances productivity
- Spring-action motion increases leverage and reduces operator fatigue
- Precision-ground, knife-type blades provide clean, accurate stripping
- Sturdy die cast frame provides long-term durability
- Wire gripper holds wire securely in position
- Stripmaster® Lite designed for smaller hands – 3/4 the size of the standard Stripmaster®



Stripmaster® Wire Stripper




Stripmaster® Lite Wire Stripper

Optional Accessories



### Stripmaster® Wire Strippers and Knife-Type Blades



Specifications — Stripping Hole Diameter (Inches)											Cat. No.	Replacement Blades (Pair) Cat. No.	
Wire Size AWG													
8	10	12	14	16	18	20	22	24	26	28	30		
.159	.141	.106										45-090* or 45-290**	L-4419
	.144	.105	.085	.073	.073							45-091	L-4420
	.144	.113	.090	.072	.061	.048	.048					45-092* or 45-292**	L-4421
			.090	.072	.061	.039	.039					45-093	L-4422
				.072	.061	.048	.039	.032	.026			45-097	L-4994
						.048	.039	.032	.026	.021	.016	45-098	L-5361
.198	.167			.062	.055							45-099	L-8763

\*Boxed \*\*Blister Card

Tolerances A.001 -.005

### Stripmaster® Lite Wire Strippers and Knife-Type Blades

Specifications — Stripping Hole Diameter (Inches)												Cat. No.	Replacement Blades (Pair) Cat. No.	
Wire Size AWG														
12	14	16	18	20	22	24	26	28	30	16/18	20/22	Cutting Edge		
		.072	.061	.048	.039								45-671	LB-1001
						.032	.026	.021	.016				45-672	LB-1002
.113	.090	.072	.061 (All stranded wire)										45-673	LB-1003
.096	.085	.073	.061 (12 & 14 Solid wire, 16 & 18 Stranded wire)										45-674	LB-1004
										.072	.048	.250 Wide	45-675	LB-1005

Tolerances A.001 -.005

### Coax Stripmaster® Wire Strippers and Blades



Description	Coax Cable Type (RGU)	Repl. Blade Cat. No.	Cat. No.
Coax Stripmaster® for RG-6	RG-6	LB-740	45-262
Coax Stripmaster® for RG-58	RG-58	LB-742	45-264
Coax Stripmaster® for RG-59	RG-59	LB-743	45-265
Coax Stripmaster® for RG-62	RG-62	LB-744	N/A
Coax Stripmaster® for RG-6 QuadShield	RG-6 QuadShield	LA-3953	45-282

Coaxial Cables: two-step strip for termination, jacket and dielectric.

Replacement Frame Assemblies	Cat. No.
For Stripmaster® Wire Strippers	L-5620
For Stripmaster® Lite Wire Strippers	LB-1421

### Stripmaster® Wire Strippers with Rectangular Holes

Description	Cat. No.	Replacement Blades (Pair) Cat. No.
For Flat Telephone Cable (.60 in. or 1.52mm)	N/A	LB-1155
For European Flat Lamp Cord	45-089	L-8762
For SP-SPT Lamp Cord	45-095*	L-4452

\*Also strips 2- and 3-conductor low-voltage wire used in G.E. and Touchplate remote control wiring system.

Optional Accessories	Cat. No.
Transparent Adjustable Wire Stop (for Stripmaster® Wire Strippers)	L-5270
Transparent Adjustable Wire Stop (for Stripmaster® Lite Wire Strippers)	LB-1195
Replacement Moveable Gripper	L-1953



### Stripmaster® Wire Strippers and Knife-Type Blades

Specifications — Stripping Hole Diameter (mm)												Cat. No.	Replacement Blades (Pair) Cat. No.	Replacement Frame Cat. No.	
Wire Size AWG															
8	10	12	14	16	18	20	22	24	26	28	30				
4	3.6	2.7											45-090 or 45-290	L-4419	L-5620
	3.6	2.7	2.2	1.8									45-091	L-4420	L-5620
	3.6	2.9	2.3	1.8	1.5	1.2							45-092 or 45-292-241*	L-4421	L-5620
			2.3	1.8	1.5	1.2	1						45-093	L-4422	L-5620
				1.8	1.5	1.2	1	0.8	0.7				45-097	L-4994	L-5620
						1.2	1	0.8	0.7	0.5	0.4		45-098	L-5361	L-5620
5	4.2			1.6	1.4								45-099	L-8763	L-5620

\*Boxed

Tolerances A.001 -.005

### Stripmaster® Lite Wire Strippers and Knife-Type Blades

Specifications — Stripping Hole Diameter (mm)													Cat. No.	Replacement Blades (Pair) Cat. No.	Replacement Frame Cat. No.	
Wire Size AWG																
12	14	16	18	20	22	24	26	28	30	16/18	20/22	Cutting Edge				
		1.8	1.5	1.2	1									45-671	LB-1001	LB-1421
						0.8	0.7	0.5	0.4					45-672	LB-1002	LB-1421
2.9	2.3	1.8	1.5 (All stranded wire)											45-673	LB-1003	LB-1421
2.4	2.2	1.9	1.5 (12 & 14 Solid wire, 16 & 18 Stranded wire)											45-674	LB-1004	LB-1421
										1.8	1.2	6.4 wide		45-675	LB-1005	LB-1421

### Stripmaster® Wire Strippers and Knife-Type Blades for Metric Wire

Specifications — Stripping Hole Diameter (mm)														Cat. No.	Replacement Blades (Pair) Cat. No.	Replacement Frame Cat. No.
Wire Size (mm²)																
0.05	0.1	0.15	0.22	0.34	0.5	0.75	1	1.5	2.5	4	6	8	10			
												4.3	5	45-090-341 or 45-290-341*	L-4419M	LA-2358
						1.3	1.6	1.9	2.4	3	3.6			45-092-341 or 45-292-341*	L-4421M	LA-2358
0.6	0.7	0.8	0.9	1	1.1									45-098-341 or 45-298-341*	L-5361M	LA-2358

\*Boxed

Tolerances A.001 -.005

### Stripmaster® Lite Wire Strippers and Knife-Type Blades for Metric Wire

Specifications — Stripping Hole Diameter (mm)										Cat. No.	Replacement Blades (Pair) Cat. No.	Replacement Frame Cat. No.			
Wire Size (mm²)															
0.05	0.1	0.15	0.22	0.34	0.5	0.75	1	1.5							
					1	1.1	1.3	1.6	1.9				45-671-341	LB-1001M	H-2909
0.6	0.7	0.8	0.9										45-672-341	LB-1002M	H-2909

Free Application Engineering Service and made-to-order Custom Stripmaster® and Stripmaster® Wire Strippers are available. Contact IDEAL INDUSTRIES, INC. for complete information at 1-800-435-0705.

Wire Strippers