



Buchanan B-TAP® Insulation Piercing Tap Connectors



Features

- Eliminates split bolts and tape
- Easy two-minute installation requires only box/socket wrench
- Torque regulating nut breaks off at proper tension
- Installs on energized systems
- Insulation piercing teeth
- Self-insulating, weather-proof
- 600V dual-rated

Models

| Wire Range | | | | Number of Bolts | Catalog Number |
|---|----------|----------|----------|-----------------|----------------------------|
| Run | | Tap | | | |
| Max. | Min. | Max. | Min. | | |
| #1/0 AWG | #8 AWG | #2 AWG | #10 AWG | 1 | BTC1/0-10 |
| #2/0 AWG | #4 AWG | #10 AWG | #14 AWG | 1 | BTC2/0-14 |
| #4/0 AWG | #2 AWG | #4/0 AWG | #2 AWG | 2 | BTC4/0-2 |
| #4/0 AWG | #3 AWG | #2 AWG | #10 AWG | 1 | BTC4/0-10 |
| #4/0 AWG | #2 AWG | #2/0 AWG | #6 AWG | 1 | BTC4/0-6 |
| 250 MCM | #1 AWG | #4/0 AWG | #4 AWG | 1 | BTC250-4 |
| 350 MCM | #1/0 AWG | 350 MCM | #1/0 AWG | 2 | BTC350-1/0 |
| 500 MCM | #2/0 AWG | #4/0 AWG | #4 AWG | 2 | BTC500-4 |
| 500 MCM | #4/0 AWG | 350 MCM | #1/0 AWG | 2 | BTC500-1/0 |
| 500 MCM | #2/0 AWG | #10 AWG | #14 AWG | 1 | BTC500-14 |
| Assortment - One of each except BTC500-14 | | | | | BTCA-2 |