




SCREW: E0940	MATERIAL:ALUMINUM, X0198	TOLERANCES-UNLESS OTHERWISE SPECIFIED 2 PL. DEC. ±.015 TRUE C.L. ±.015 3 PL. DEC. ±.015 ANGLES ±1		DWG. NO. D1548		
CAT. NO.:T3A4-3/0N	PLATING: EL-TIN	DRAWN BY:CLH	SCALE: 1:1	SHEET 1 OF 1		
MASS:.428 LBS.	MARKING: ILSCO, T3A4-3/0N, 3/0-6, AL9CU  	DATE:1/2/2008	SIZE: A			
SURFACE AREA: 35.691 IN ²		CELL:AMP				
STUFFER SHT: FORM 1					REV. G	DESCRIPTION

Cat #: T3A4-3/0N

