



Actual

Catalog Number: ADR60
Product ID: 7TAH006600R0233
UPC Number: 78378661031
EAN Number: 05414363147534
Status: Active

Type ADR-ALCUL Single-Conductor, One-Hole Mount, Conductor Range Max 600 kcmil, Min 2 Str, 3/8 Inch Bolt Hole, Length 3-3/16 Inch, Tin Plated

- Easy Installation - no special tools required.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Dual-Rated Mechanical Connector
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Number Of Conductors	1
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	2-600
Number Of Mounting Holes	1
Mounting Hole Spacing	3/8 Inch

Packaging

Inner Quantity	6
Inner Dimensions (inches)	6.7x3.8x5.1
Outer Quantity	60
Outer Dimensions (inches)	15.1x8.2x5.9
Weight Uom	35 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000391

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com