



Representative

**Catalog Number:** ATL500-12  
**Product ID:** 7TAH007610R0092  
**UPC Number:** 78378661112  
**EAN Number:** 05415022239706  
**Status:** Active

Type Aluminum One-Hole Lug, Max 35kV, Wire Size 500 kcmil, 1/2 Inch Bolt Hole, Tin Plated, Die Color Code Pink

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Aluminum Lug
Special Features	Aluminum Lug
Standard	UL E9809
Stud Size	1/2 Inch
Number Of Holes	1
Voltage Rating	35KV
Material	Aluminum
Color	Pink

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
With sight-hole	N
Surface protection	Tinned
Number of fixing holes	1

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	5.5x4x3
Outer Quantity	50
Weight Uom	23.75 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000516

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)